

LINE, LOAD & NEUTRAL LUGS
4 PER POLE PROVIDED FOR 1200 AMP (1) 1/0 AWG OR (2) 300 kcmil
8 PER POLE PROVIDED FOR 2000 AMP
8 PER POLE PROVIDED FOR 2000 AMP

5. NEUTRAL INSULATED, BONDABLE.

7. SHORT CIRCUIT CURRENT RATINGS:

100,000 RMS SYMMETRICAL AMPERES, 240 VAC WHEN

6. 100% LOAD BREAK RATED.

USED WITH CLASS L FUSES.
8. DUAL DIMENSIONS, INCHES [MILLIMETERS].

8 PER POLE PROVIDED FOR 2000 AMP REF NO CAT NO DWG DATE
GROUND LUG (5 PROVIDED) #6 AWG 250 kcmil AL OR CU
96-7084 TMP3FT16R 1/8/2015

METER MOD III–1600A MAIN FUSIBLE SWITCH N3R ENCL

100KAIC 3PH 4W 208Y/120V TOP ONLY FEED

REV#

01