

MAIN SWITCH MODULE

CATALOG NO. TMP3FT6R
TYPE 3R ENCLOSURE - RAINPROOF - 600AMP.
120/240V AC 1 PHASE-3 WIRE
208Y/120V AC 3 PHASE-4 WIRE
240/120V AC 3 PHASE-4 WIRE

For use with TMP or TMPR meter modules and TMP main lug modules. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

REPLACEMENT PARTS

End Cap - Right (Deep)	TMECR
End Cap - Left (Flat)	TMECL
Switch Assembly (Complete)	TMP3FTS6
Front Cover	TMFC2
Drip Hood	TMDH9
Handle	TMPFH1
Hardware Kit	TMPMSK1
Shroud	TMPSH1

TORQUE MAIN BUS JOINT BOLTS 300 LB-INS

Suitable only for top feed.
Order rainproof hubs from table below.

Conduit Size	Cat.No.
1/2	343L647G3
3/4	343L647G4
1	343L647G5
1-1/4	343L647G6
1-1/2	343L647G7
2	343L647G8
2-1/2	343L647G9
3	343L647G10
3-1/2	343L647G11
4	343L647G12

**SUITABLE FOR USE AS
SERVICE EQUIPMENT**

**USE COPPER OR
ALUMINUM WIRE**
USE 75°C WIRE

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque, Lb.-Ins.
Line Terminals	(2) 2-600	500
Neutral Terminal	(2) 2-600	500
Grounding Terminal	4-300	250

SHORT CIRCUIT CURRENT RATING

This module is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module.

