

METER MODULE

CATALOG NO. TMP8120RTAB

TYPE 3R ENCLOSURE - RAINPROOF


MAIN BUS - 1200 AMPS MAX
120/240 VAC 1 PH - 3W
208Y/120 VAC 3 PH - 4W

BRANCH BREAKERS: 200A MAX.

METER SOCKET RATING:
200 AMPS CONTINUOUS

THIS METER MODULE MEETS
EUSERC REQUIREMENTS.

USE WITH TMP MAIN SWITCH,
MAIN BREAKER, MAIN LUG,
OR METER MODULES



TYPICAL DIAGRAM

USE ONLY GENERAL ELECTRIC
TYPE TQD, THQD, TMQV, TEB, TED,
OR THED CIRCUIT BREAKERS.

SUITABLE FOR USE AS SERVICE
EQUIPMENT WHEN USED WITH
TMP MAIN LUG MODULES AND
WHEN NOT MORE THAN SIX
MAIN DISCONNECTING MEANS
ARE PROVIDED.

TORQUE MAIN BUS JOINT BOLTS
TO 300 LB-IN

RAINTIGHT HUBS

CONDUIT SIZE	CATALOG NUMBER	CONDUIT SIZE	CATALOG NUMBER
1/2	343L647G3	2	343L647G8
3/4	343L647G4	2-1/2	343L647G9
1	343L647G5	3	343L647G10
1-1/4	343L647G6	3-1/2	343L647G11
1-1/2	343L647G7	4	343L647G12

SUITABLE FOR TOP OR BOTTOM FEED. FOR TOP
FEED, USE RAIN TIGHT HUBS PER TABLE ABOVE.

USE 60/75°C AL-CU WIRE

LUG SPECIFICATIONS

FUNCTION	WIRE SIZE AL-CU AWG/MCM	TORQUE LB-IN
NEUTRAL	(2) 1/0-300	200
EQUIPMENT GROUND	(2) { 6-4 3-2/0	45 50

TORQUE BREAKER LUGS TO THE VALUE
SPECIFIED ON BREAKERS.

REPLACEMENT PARTS

TENANT BREAKER COVER	TMBC20
BREAKER MOUNTING KIT	TMTQD3
HARDWARE KIT	TMP3SK

GENERAL  **ELECTRIC**