




Front View



Front Layout View



Side View




This unit uses a standard/disconnect style fusible switch. This unit uses only T fuses

Incoming Cable Sizes:

(4) #2-500MCM per Ph/Neutral (AL/CU)

| | (4) 500 KCMIL | (3) 750 KCMIL |
|------------------------|---------------|---------------|
| WIRE BENDING - PHASE | 20.70 | 21.06 |
| WIRE BENDING - NEUTRAL | 17.68 | 19.06 |

1 KNOCKOUT FOR 3/4"(19), 1"(25), 1-1/4"(32), OR 1-1/2"(38) CONDUIT



Bottom View



imagination at work

METER MOD III-1200A MAIN FUSIBLE SWITCH N3R ENCL
100KAIC 1PH 3W 120/240V BOTTOM ONLY FEED

| REF NO | CAT NO | DWG DATE | REV # |
|---------|-----------|----------|-------|
| 96-3831 | TMPFB12RT | 1/8/2015 | 01 |