

MAIN SWITCH MODULE WITH INTEGRAL PULL BOX

CATALOG NO. TMPFB8RCLL
TYPE 3R ENCLOSURE — RAINPROOF — 800 AMP.
120/240V AC 1 PHASE — 3 WIRE

For use with TMP or TMPR meter modules and TMP main lug modules. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

REPLACEMENT PARTS		SUITABLE FOR USE AS SERVICE EQUIPMENT
End Cap — Right (Deep)	TMECR	USE COPPER OR ALUMINUM WIRE USE 75°C WIRE
End Cap — Left (Flat)	TMECL	
Switch Assembly (Complete)	TMFBS8	TORQUE MAIN BUS JOINT BOLTS 300 LB-INS
Front Cover (Top)	TMFCT	
Front Cover (Bottom)	TMFCB	
Drip Hood	TMDH9	Suitable only for bottom feed.
Handle	TMPFH1	
Hardware Kit	TMPMSK1	
Shroud	TMPSH1	

LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque lb.-ins.
Grounding Terminal	4-300	250

SHORT CIRCUIT CURRENT RATING

This switch module may be used only with Class T fuses and is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module.

The following U.L. Listed crimp connectors may be used:

Wire Size (CU Only)	Manufacturer & Cat. No.			
	Mac	T & B	Burndy	Panduit
250MCM	MSB250-8N	54275	YA29-2LN	LCC250-12
	MRB250-8N	54868BE	YA29-2N	
300MCM	MSB300-8N	54260	YA30-2LN	LCC300-12
	MRB300-8N	54870BE	YA30-2N	
350MCM	MSB350-8N	54282	YA31-2LN	LCC350-12
	MRB350-8N	54872BE	YA31-2N	
400MCM	MSB400-8N	54874BE	YA32-2LN	LCC400-12
	MRB400-8N		YA32-2N	
500MCM	MSB500-8N	54266	YA34-2LN	LCC500-12
	MRB500-8N	54876BE	YA34-2N	
600MCM	MSB600-8N	54289	YA36-2LN	—
	MRB600-8N	54878BE	YA36-2N	
700MCM	—	54291	—	—
750MCM	MSB750-8N	54223	YA39-2LN	LCC750-12
	MRB750-8N	54880BE	YA39-2N	
Wire Size (AL/CU)				
250MCM	MLB250-8N	60256	YA29A3	LAB250-12
	MULB250-8N		YA29AY-2N	
300MCM	MLB300-8N	60262	YA30A3	LAB300-12
	MULB300-8N		YA30AY-2N	
350MCM	MLB350-8N	60267	YA31A3	LAB350-12
	MULB350-8N		YA31AY-2N	
400MCM	MLB400-8N	60269	YA32A3	LAB400-12
	MULB400-8N		YA32AY-2N	
500MCM	MLB500-8N	60273	YA34A3	LAB500-12
	MULB500-8N		YA34AY-2N	
600MCM	MLB600-8N	60275	YA36A3	LAB600-12
	MULB600-8N		YA36AY-2N	
700MCM	—	60277	—	—
750MCM	—	—	YA39A5	LAB750-12

Torque 1/2-13 crimp lug mounting nuts to 40-44 lb.-ft.

GENERAL ELECTRIC