

# METER MODULE

CATALOG NO. TMPR12422R

TYPE 3R ENCLOSURE – RAINPROOF

MAIN BUS – 1200 AMPS MAX  
120/240 VAC 1 PH – 3W  
208Y/120 VAC 3 PH – 4W

**BRANCH BREAKERS:**

TYPE TMQV – 225 AMPS MAX.  
TYPE THQD – 200 AMPS MAX.  
TYPE TQD – 200 AMPS MAX.

METER SOCKET RATING:  
200 AMPS CONTINUOUS

USE ONLY GENERAL ELECTRIC  
TYPE TQD, THQD, TMQD, TEB, TED,  
OR THED CIRCUIT BREAKERS.

SUITABLE FOR USE AS SERVICE  
EQUIPMENT WHEN USED WITH  
TMP MAIN LUG MODULES AND  
WHEN NOT MORE THAN SIX  
MAIN DISCONNECTING MEANS  
ARE PROVIDED.

USE WITH TMP MAIN SWITCH,  
MAIN BREAKER, MAIN LUG,  
OR METER MODULES

**TORQUE MAIN BUS JOINT BOLTS  
TO 300 LB-IN**

**RAINTIGHT HUBS**

CONDUIT SIZE	CATALOG NUMBER	CONDUIT SIZE	CATALOG NUMBER
1/2	343L647G3	2	343L647G8
3/4	343L647G4	2-1/2	343L647G9
1	343L647G5	3	343L647G10
1-1/4	343L647G6	3-1/2	343L647G11
1-1/2	343L647G7	4	343L647G12

SUITABLE FOR TOP OR BOTTOM FEED. FOR TOP  
FEED, USE RRAINTIGHT HUBS PER TABLE ABOVE.

**USE 60/75°C AL-CU WIRE**


**LUG SPECIFICATIONS**

FUNCTION	WIRE SIZE AL-CU AWG/MCM	TORQUE LB-IN
NEUTRAL	(4) 1/0-300	200
EQUIPMENT GROUND	(4) { 14-10 8 6-4 3-2/0	35 40 45 50

TORQUE BREAKER LUGS TO THE VALUE  
SPECIFIED ON BREAKERS.

**REPLACEMENT PARTS**

METER SOCKET	TMSR22
METER SOCKET COVER	TMCR322
TENANT BREAKER COVER	TMBC20
WIREWAY COVER	TMWC3422
DRIP HOOD	TMDH4
KO PLATE – BACK	TMKPB322
KO PLATE – TOP/BOTTOM	TMKPT322
BREAKER MOUNTING KIT	TMTQD3
HARDWARE KIT	TMP3SK



**TYPICAL DIAGRAM**

**GENERAL ELECTRIC**