

METER MODULE

CATALOG NO. TMPR312422R

TYPE 3R ENCLOSURE – RAINPROOF

MAIN BUS – 1200 AMPS MAX
 120/240 VAC 1 PH – 3W
 208Y/120 VAC 3 PH – 4W
 240/120 VAC 1 PH – 4W

BRANCH BREAKERS:
 TYPE TMQV – 225 AMPS MAX.
 TYPE THQD – 200 AMPS MAX.
 TYPE TQD – 200 AMPS MAX.

METER SOCKET RATING:
 200 AMPS CONTINUOUS

USE WITH TMP MAIN SWITCH,
 MAIN BREAKER, MAIN LUG,
 OR METER MODULES

USE ONLY GENERAL ELECTRIC
 TYPE TQD, THQD, TMQD, TEB, TED,
 OR THED CIRCUIT BREAKERS.

SUITABLE FOR USE AS SERVICE
 EQUIPMENT WHEN USED WITH
 TMP MAIN LUG MODULES AND
 WHEN NOT MORE THAN SIX
 MAIN DISCONNECTING MEANS
 ARE PROVIDED.

**TORQUE MAIN BUS JOINT BOLTS
 TO 300 LB-IN**

RAINTIGHT HUBS

CONDUIT SIZE	CATALOG NUMBER	CONDUIT SIZE	CATALOG NUMBER
1/2	343L647G3	2	343L647G8
3/4	343L647G4	2-1/2	343L647G9
1	343L647G5	3	343L647G10
1-1/4	343L647G6	3-1/2	343L647G11
1-1/2	343L647G7	4	343L647G12

SUITABLE FOR TOP OR BOTTOM FEED. FOR TOP FEED, USE RRAINTIGHT HUBS PER TABLE ABOVE.

USE 60/75°C AL-CU WIRE


LUG SPECIFICATIONS

FUNCTION	WIRE SIZE AL-CU AWG/MCM	TORQUE LB-IN
NEUTRAL	(4) 1/0-400	200
EQUIPMENT GROUND	(4) { 14-10 8 6-4 3-2/0	{ 35 40 45 50

TORQUE BREAKER LUGS TO THE VALUE SPECIFIED ON BREAKERS.

REPLACEMENT PARTS

METER SOCKET	TMSR322
METER SOCKET COVER	TMCR322
TENANT BREAKER COVER	TMBC20
WIREWAY COVER	TMWC3422
DRIP HOOD	TMDH4
KO PLATE – BACK	TMKPB322
KO PLATE – TOP/BOTTOM	TMKPT322
BREAKER MOUNTING KIT	TMTQD3
HARDWARE KIT	TMP3SK



Ø IS HIGH LEG (POWER LEG) FOR 3PH – 4W DELTA SYSTEM
 □ EQUIPMENT GROUND

TYPICAL DIAGRAM

GENERAL ELECTRIC