

BUSSED SPACER

CATALOG NO. TMPS12
TYPE 3R ENCLOSURE - RAINPROOF
1200A MAX.
120/240 VAC 1PH-3W
208Y/120 VAC 3PH-4W
240/120 VAC 3PH-4W, DELTA

FOR USE WITH TMP OR TMPR METER
SOCKET/CIRCUIT BREAKER MODULES, TMP
MAIN TERMINAL BOXES, TMP MAIN
SWITCHES, AND TMP MAIN BREAKERS.

TORQUE MAIN BUS JOINT BOLTS
25 LB.-FT. (300 LB.-IN.)

SHORT CIRCUIT CURRENT RATING
THIS BUSSED SPACER IS UL LISTED FOR THE
FOLLOWING SHORT CIRCUIT CURRENT
RATINGS IN RMS SYMMETRICAL AMPERES AT
240 VAC MAXIMUM.

100,000 AIC WHEN USED WITH A
TMP MAIN SWITCH.

100,000 AIC WHEN USED WITH A
TMP OR TMPR
METER MODULE.

42,000 AIC WHEN USED WITH A
TMP MAIN CIRCUIT BREAKER.

THE SHORT CIRCUIT CURRENT RATING IS
LIMITED TO THE LOWEST MARKED SHORT
CIRCUIT RATING OF THE MAIN SWITCH, MAIN
CIRCUIT BREAKER, OR THE METER MODULE
USED.

E26632

GENERAL  **ELECTRIC**

MADE IN USA

PUB 19579

REV 2