

# GENERAL ELECTRIC

## MAIN PULL BOX MODULE - TMPU12R

**1200 AMPS MAX**  
**120/240 VAC, 1PH-3W**

### TYPE 3R ENCLOSURE - RAINPROOF

SUITABLE FOR UNDERGROUND FEED ONLY

INSTALLATION AND USE OF THIS EQUIPMENT SHOULD CONFORM TO ALL LOCAL AND NATIONAL CODES AND REGULATIONS.

FOR USE WITH GENERAL ELECTRIC MAIN SWITCHES OR MAIN CIRCUIT BREAKERS.

### SHORT CIRCUIT CURRENT RATING

WHEN USED WITH A GENERAL ELECTRIC MAIN SWITCH OR MAIN CIRCUIT BREAKER, THIS PULL BOX IS SUITABLE FOR USE ON CIRCUITS CAPABLE OF DELIVERING NOT MORE THAN 100,000 RMS SYMMETRICAL AMPERES, 240 VOLTS MAX. THE SHORT CIRCUIT RATING IS LIMITED TO THE LOWEST MARKED SHORT CIRCUIT CURRENT RATING OF THE MAIN SWITCH OR MAIN BREAKER USED WITH THIS PULL BOX.

USE 75°C AL-CU CONDUCTORS - TORQUE AS SHOWN BELOW:

LINE TERMINALS: TORQUE 1/2" NUTS TO 45 FT.-LB. (61.01 N-m)

LOAD TERMINALS: (4) 2-600 MCM 375 IN.-LB. (42.37 N-m)

#### THE FOLLOWING UL LISTED CRIMP CONNECTORS MAY BE USED

THE FOLLOWING UL LISTED CRIMP CONNECTORS MAY BE USED				
WIRE SIZE				
CU ONLY	MAC	T & B	BURNDY	PANDUIT
250 kcmil	MSB250-8N MRB250-8N	54275 54868BE	YA29-2LN YA29-LN	LCC250-12
300 kcmil	MSB300-8N MRB300-8N	54280 54870BE	YA30-2LN YA30-LN	LCC300-12
350 kcmil	MSB350-8N MRB350-8N	54282 54872BE	YA31-2LN YA31-LN	LCC350-12
400 kcmil	MSB400-8N MRB400-8N	54874BE	YA32-2LN YA32-LN	LCC400-12
500 kcmil	MSB500-8N MRB500-8N	54286 54876BE	YA34-2LN YA34-LN	LCC500-12
600 kcmil	MSB600-8N MRB600-8N	54289 54878BE	YA36-2LN YA36-LN	_____
700 kcmil	_____	54291	_____	_____
750 kcmil	MSB750-8N MRB750-8N	54223 54880BE	YA39-2LN YA39-LN	LCC750-12
AL-CU				
250 kcmil	MLB250-8N MULB250-8N	60256	YA29A3 YA29AY-2N	LAB250-12
300 kcmil	MLB300-8N MULB300-8N	60262	YA30A3 YA30AY-2N	LAB300-12
350 kcmil	MLB350-8N MULB350-8N	60267	YA31A3 YA31AY-2N	LAB350-12
400 kcmil	MLB400-8N MULB400-8N	60269	YA32A3 YA32AY-2N	LAB400-12
500 kcmil	MLB500-8N MULB500-8N	60273	YA34A3 YA34AY-2N	LAB500-12
600 kcmil	MLB600-8N MULB600-8N	60275	YA36A3 YA36AY-2N	LAB600-12
700 kcmil	_____	60277	_____	_____
750 kcmil	_____	_____	YA39A5	LAB750-12

NOTE: TORQUE 1/2" NUTS WHICH ATTACH CRIMP CONNECTORS TO 45 FT.-LB. (61 N-m)