



Top View




Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-2	12-8	12-2
LOAD	14-8	14-2	12-8	12-2
NEUTRAL	-----	-----	-----	-----
EQUIP. GRND.	12-8	12-2	12-8	12-2


Left Side View




Front View Interior




Front View Inside Cover




Front View External Cover



Right Side View



Bottom View





Knockouts

L= 1/2", 3/4" KØ
G= 1/2", 3/4", 1" KØ
M= 1/2", 3/4", 1", 1-1/4" KØ

Receptacles

5-15R2GFI

	Industrial Solutions	
60A GD AC DISCONNECT NON-AUTO SWITCH 15A GFI RECEPT NON-FUSIBLE 1PH 10HP STEEL N3R ENCLOSURE		
CAT NO TNA60RGFR	DWG DATE 04/07/2020	REV# 03