




Top View



**Front View
Inside Cover**




Bottom View




Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-6	12-8	12-6
LOAD	14-10	14-10	-----	-----
NEUTRAL	12-8	12-6	12-8	12-6
EQUIP. GRND.	12-8	12-2	12-8	12-2


Left Side View



**Front View
External**



Right Side View




Receptacles

5-20R2GFCI

Circuit Protection


THQL1120

Configuration



Knockouts

S= 1/2", 3/4", 1", 1-1/4", 1-1/2" KO
G= 1/2", 3/4", 1" KO



Midwest Electric Products
Plainville, CT

MIDWEST RV EQUIP METALLIC SURFACE MT 20A
GFCI UNMTERED 120V 1PH3W UL LISTED G90 N3R

CAT NO	DWG DATE	REV #
U010C010	07/12/2016	01