



**Top View**




**Knockouts**

L= 1/2", 3/4" KO  
 M= 1/2", 3/4", 1", 1-1/4" KO  
 G= 1/2", 3/4", 1" KO


**Left Side View**




**Front View Inside Cover**




**Front View External Covers**




**Right Side View**




**Front View Interior**



**Bottom View**



**Configuration**



**Receptacles**

5-20R2GFCI

**Wire Range Size**

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-10	14-10	-----	-----
LOAD	14-10	14-10	-----	-----
NEUTRAL	14-10	14-10	-----	-----
EQUIP. GRND.	12-8	12-2	-----	-----



Midwest Electric Products  
 Plainville, CT

MIDWEST POWER OUTLETS SURFACE MOUNT 20A  
 GFCI 120V 1PH N3R G90

CAT NO	DWG DATE	REV #
U010SEP	07/12/2016	01