


**Front View
Inside Cover**


Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	14-8	14-2	12-8	12-2
LOAD	14-10	14-10	-----	-----
NEUTRAL	14-8	14-2	12-8	12-2
NEUTRAL	14-8	14-4	12-8	12-4
EQUIP. GRND.	12-8	12-2	12-8	12-2


Left Side View




**Front View
Interior**




**Front View
External**




Right Side View



Bottom View



Configuration



Receptacles

(2) 5-20R2GFCI

Circuit Protection

(2) THQL1120
Space THQL1120

Knockouts

S= 1/2", 3/4", 1", 1-1/4", 1-1/2" KO
G= 1/2", 3/4", 1" KO

Midwest Electric Products
Plainville, CT

MIDWEST RV EQUIP METALLIC SURFACE MT 70A
GFCI UNMTERED 120/V 1PH3W UL LISTED G90
N3R

CAT NO	DWG DATE	REV #
U011C010	07/12/2016	01