



### Top View




### Wire Range Table

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-2	12-8	12-2
LOAD	14-8	14-2	12-8	12-2
NEUTRAL	-----	-----	-----	-----
EQUIP. GRND.	12-8	12-2	12-8	12-2


### Left Side View



### Front View




### Front Cover




### Front View



### Right Side View



### Bottom View



### Knockouts

G = 1/2", 3/4", 1" KO
S = 1/2", 3/4", 1", 1-1/4", 1-1/2" KO



MIDWEST 30A GD DISCONNECT PULLER TYPE 1PH 240V 3HP  
FUSIBLE 20A GFI RECEPT STEEL N3R ENCLOSURE

CAT NO	DWG DATE	REV #
U035F010	2/4/2016	01