



Wire Range Size

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRANDED	SOLID	STRANDED
LINE	14-10	14-10	-----	-----
LOAD	14-10	14-10	-----	-----
NEUTRAL	14-10	14-10	-----	-----
EQUIP. GRND.	12-8	12-2	-----	-----


Top View




Left Side View




Back View




Inside Receptacle View




Front View



Right Side View



Bottom View



Circuit Protection

None

Receptacles

CS6375*

Knockouts

G= 1/2", 3/4", 1" KO
 S= 1/2", 3/4", 1-1/4", 1-1/2" KO

*California Standard, three pole, 4 wire grounded non-NEMA



Midwest Electric Products
 Plainville, CT

MIDWEST POWER INLET 50A 1PH 120/240V N3R G90
 STEEL ENCLOSURE

CAT NO	DWG DATE	REV #
U050N	03/22/2017	01