



Top View




Knockouts

| |
|--------------------------------------|
| G= 1/2", 3/4", 1" KØ |
| S= 1/2", 3/4", 1", 1-1/4", 1-1/2" KØ |


Left Side View




Front Interior




Front Cover



Right Side View



Bottom View



Wire Range Size

| CONNECTOR | COPPER | | ALUMINUM | |
|--------------|--------|--------|----------|--------|
| | SOLID | STRAND | SOLID | STRAND |
| LINE | 14-8 | 14-2 | 12-8 | 12-2 |
| LOAD | 14-8 | 14-2 | 12-8 | 12-2 |
| NEUTRAL | ----- | ----- | ----- | ----- |
| EQUIP. GRND. | 12-8 | 12-2 | 12-8 | 12-2 |



MIDWEST 60A GD AC DISCONNECT PULLER-TYPE 3PH 240V NON-FUSIBLE 15A RECEPT 15HP STEEL N3R ENCL

| CAT NO | DWG DATE | REV # |
|-----------|------------|-------|
| U0653P010 | 04/10/2016 | 02 |