



### Top View




### Wire Range Table

CONNECTOR	COPPER		ALUMINUM	
	SOLID	STRAND	SOLID	STRAND
LINE	14-8	14-1/0	12-8	12-1/0
LOAD	14-8	14-2	12-10	12-2
NEUTRAL	14-8	14-1/0	12-8	12-1/0


### Left Side View




### Front View (Inside)




### Front Cover




### Front View (Outside)



### Right Side View



### Bottom View



### Knockouts

B= 1", 1-1/4", 1-1/2" K□
D= 3/4", 1", 1-1/4" K□
G= 1/2", 3/4", 1" K□
H= 9/32" K□



MIDWEST HEAT PUMP 100A (DUAL 60A) PULLER-TYPE FUSIBLE 10HP N3R ENCLOSURE 1PH 120/240V UL LISTED

CAT NO	DWG DATE	REV #
U610F	2/4/2016	01