





Left Side View



Front View



Right Side View



Bottom View

Notes

- 1) FINISH: NATURAL
- 2) CABINET: 0.63 ALUMINUM
- 3) 200 AMP CONTINUOUS, 600 VAC, 1 PHASE, 3 WIRE
- 4) FOR BROOKS OR INNER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH BROOKS LOCK GUARDS # 865 OR # 86505 WITH PERMANENTLY WELDED BRACKET
- 5) GE CARTON LABEL ATTACHED TO THE END OF THE CARTON
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 7) GE SAFETY LABEL PLACED IN THE LOWER LEFT-HAND CORNER OF FRONT

GE is a registered trademark used under license from General Electric company.



METER SOCKET-(1) 200A 600V 1P3W ALUM N3R 4-TERM
SOLID TOP HORN BYP AEP BARREL LK BOTTOM FED

CAT NO	DWG DATE	REV #
UAFHTRS223ASHGE	08/22/2016	01