




Left Side View



Front View Interior



Right Side View




Notes

- 1) FINISH: NATURAL
- 2) CABINET: .080 ALUMINUM
- 3) 320 AMP CONTINUOUS, 600 VAC, 3 PHASE 3 WIRE,
1 PHASE 3-WIRE, NETWORK 3-WIRE, 320A BYPASS
- 4) GE LABEL ATTACHED TO THE END OF THE CARTON
- 5) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 6) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF THE FRONT

Bottom View

STAINLESS STEEL
LATCH TAB



METER SKT-(1) 320A 600V 3P3W or 1P3W ALUM N3R 5-TERM
LARGE HB COVER PLT TOP/BOT FEED LEVER BYP TPLX GRD MEG

CAT NO	DWG DATE	REV #
UATH5330UFLGE	06/13/2016	01