


Left Side View




Neutral Stud Detail



3-1/2, 3, 2-1/2, 2 KO
(6) PLACES

STAINLESS
STEEL
RIBBON SEAL
ROTARY LATCH

Front View Interior




Notes

- 1) FINISH: NATURAL
- 2) CABINET: .080 ALUMINUM
- 3) 320 AMP CONTINUOUS, 600 VAC, 3 PHASE 4 WIRE, 320A BYPASS
- 4) GE LABEL ATTACHED TO THE END OF THE CARTON
- 5) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 6) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF THE FRONT

Bottom View

STAINLESS STEEL
LATCH TAB



METER SKT-(1) 320A 600V 3P4W ALUM N3R 7-TERM LARGE HUB
OPENING TOP/BOT FEED LEVER BYP TPLX GRD MEG APPROVED

CAT NO	DWG DATE	REV #
UATH7300TFLGE	06/13/2016	01