



### Front View




### Side View



### Notes

- 1) FINISH: GRAY
- 2) CABINET: 16GA GALV STEEL
- 3) 200 AMP CONTINUOUS, 600 VAC, 3 PHASE, 4 WIRE, 200 AMP BYPASS
- 4) FOR AN EXPOSED INNER-TITE OR BROOKS STANDARD LENGTH BARREL LOCK WITH A PERMANENTLY WELDED BRACKET
- 5) GE LABEL ATTACHED TO THE END OF THE CARTON
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 7) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF THE FRONT

### Bottom View



GE is a registered trademark used under license from General Electric company.



METER SOCKET - (1) 200A 600V 3P4W N3R G90 7-TERM  
BARREL LOCK LARGE HUB OPN LVR BYP TOP/BOT FEED

CAT NO	DWG DATE	REV #
UBH7213TGE	02/10/2016	01