



Front View




Side View




Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV. STEEL
- 3) 125 AMP CONTINUOUS, 600 VAC, 1 PHASE, 3-WIRE
- 4) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 5) FOR AN EXPOSED INNER-TITE OR BROOKS STANDARD LENGTH BARREL LOCK WITH A PERMANENTLY WELDED BRACKET
- 6) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
- 7) MIDWEST LOGO LOCATED IN THE LOWER LEFT-HAND CORNER OF THE FRONT.

Bottom View





METER SOCKET - (1) 125A 600V 1P3W N3R G90 4-TERM
HUB OPN HORN BYP AEP BARRELL LOCK TOP/BOT FEED

CAT NO	DWG DATE	REV #
UBHRS101BMEP	02/10/2016	01