



Front View




Side View




Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV. STEEL
- 3) 200 AMP CONTINUOUS
600 V.A.C., 1 PHASE, 3 WIRE
- 4) FOR AN EXPOSED INNER-TITE
OR BROOKS STANDARD LENGTH
BARREL LOCK WITH A PERMANENTLY
WELDED BRACKET
- 5) MIDWEST LABEL ATTACHED
TO THE END OF CARTON
- 6) TEMPORARY CARDBOARD METER
OPENING COVER PROVIDED
- 7) MIDWEST LOGO STAMPED ON LOWER
LEFT-HAND CORNER OF FRONT

Bottom View



		
METER SOCKET - (1) 200A 600V 1P3W N3R G90 4-TERM HUB OPNG HORN BYP AEP BARREL LOCK TOP/BOT FEED		
CAT NO	DWG DATE	REV #
UBHRS212BMEP	02/10/2016	01