




Left Side View



Front View Interior



Bottom View



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV STEEL
- 3) 200 AMP CONTINUOUS PER POSITION
600 VAC, 1 PHASE, 3-WIRE
360AMP CONTINUOUS (TOTAL) UNIT RATING
WITH COPPER WIRE
310 AMP CONTINUOUS (TOTAL) UNIT RATING
WITH ALUMINUM WIRE
- 4) FOR BROOKS OR INNER-TITE
STANDARD LENGTH BARREL LOCK
IN CONJUNCTION WITH BROOKS
LOCK GUARDS #865 OR #86505
WITH A PERMANENTLY WELDED
BRACKET
- 5) MIDWEST LABEL ATTACHED
TO THE END OF THE CARTON.
- 6) TEMPORARY CARDBOARD METER OPENING
COVERS PROVIDED.
- 7) MIDWEST LOGO STAMPED IN THE
LOWER LEFT-HAND CORNER OF FRONTS.



HORIZ GANGED MTR SKTS-(4) 200A 600V 1P3W N3R LARGE HUB
OPNG HORN BYP AEP BRL LK 4-TRM CENTER FEED G90 TPLX GRD

CAT NO	DWG DATE	REV #
UFHT4R2352TMEP	06/09/2016	01