



### Left Side View




7/8 DIA KO FOR BARREL LOCK

### Front View Interior



### Bottom View



### Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV STEEL
- 3) 200 AMP CONTINUOUS PER POSITION  
600 VAC, 1 PHASE, 3-WIRE  
620 AMP CONTINUOUS (TOTAL) UNIT RATING
- 4) FOR BROOKS OR INNER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH BROOKS LOCK GUARDS #865 OR #86505 WITH A PERMANENTLY WELDED BRACKET
- 5) TEMPORARY CARDBOARD METER OPENING COVERS PROVIDED.
- 6) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
- 7) MIDWEST LOGO STAMPED IN LOWER LEFT HAND CORNER OF THE FRONTS.



HORIZ GANGED MTR SKTS-(6) 200A 600V 1P3W N3R 2-LARGE HUB OPNG HORN BYP AEP BRL LK 4-TRM CENTER FEED G90 TPLX GRD

CAT NO	DWG DATE	REV #
UFHT6R2392TTMEP	06/09/2016	01