



Left Side View




Front View Interior



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV. STEEL
- 3) 125 AMP CONTINUOUS, 600 VAC, 1 PHASE, 3-WIRE
- 4) MIDWEST LABEL ATTACHED TO THE END OF THE CARTON.
- 5) MIDWEST LOGO STAMPED IN THE LOWER LEFT-HAND CORNER OF FRONT.
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED.
- 7) FOR BROOKS OR INNER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH A BROOKS LOCK GUARDS #865 OR #86505, WITH A PERMANENTLY WELDED BRACKET.

Bottom View



METER SKT-(1)125A 600V 1P3W G90 N3R 4-TERM SMALL HUB OPNG TPLX GRD HORN BYP AEP BARREL LK TOP/BOT FEED

CAT NO	DWG DATE	REV #
UFHTRS101BMEP	05/24/2016	02