



Front View




Side View



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16GA GALV. STEEL
- 3) 200 AMP CONTINUOUS
600 VAC, 1 PHASE, 3 WIRE
200 AMP BYPASS
- 4) MIDWEST LABEL ATTACHED TO THE
END OF THE CARTON
- 5) TEMPORARY CARDBOARD METER OPENING
COVER PROVIDED
- 6) MIDWEST LOGO STAMPED IN THE LOWER
LEFT-HAND CORNER OF THE FRONT
- 7) FOR BROOKS OR INNER-TITE STANDARD
LENGTH BARREL LOCK IN CONJUNCTION
WITH A BROOKS LOCK GUARD #865 OR
#86505, WITH A PERMANENTLY WELDED
BRACKET.

Bottom View



METER SKT-(1) 200A 600V 1P3W N3R G90 4-TERM SMALL HUB
CVR PLT TPLX GRD LVR BYP AEP BARREL LK TOP/BOT FEED

CAT NO	DWG DATE	REV #
UFTH4213CMEP	02/10/2016	01