




Left Side View



Front View Interior




Line Bus Detail



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16GA GALV STEEL
- 3) 320 AMP CONTINUOUS, 600 VAC, 1 PHASE, 3 WIRE, 320 AMP BYPASS
- 4) FOR BROOKS OR INNER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH A BROOKS LOCK GUARDS # 865 OR # 86505 WITH A PERMANENTLY WELDED BRACKET
- 5) GE LABEL ATTACHED TO THE END OF THE CARTON
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 7) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF THE FRONT

Bottom View



METER SKT-(1) 320A 600V 1P3W G90 N3R 4-TERM LARGE HUB OPENING TOP/BOT FED TPLX GRD AEP BARREL LK LEVER BYP

GE is a registered trademark used under license from General Electric company.

CAT NO	DWG DATE	REV #
UFTH4330TGE	06/20/2016	01