



Left Side View




Front View Interior



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16GA GALV. STEEL
- 3) 200 AMP CONTINUOUS
600 VAC, 3 PHASE, 4 WIRE
200 AMP BYPASS
- 4) MIDWEST LABEL ATTACHED TO THE
END OF THE CARTON
- 5) TEMPORARY CARDBOARD METER OPENING
COVER PROVIDED
- 6) MIDWEST LOGO STAMPED IN THE LOWER
LEFT-HAND CORNER OF THE FRONT
- 7) FOR BROOKS OR INNER-TITE STANDARD
LENGTH BARREL LOCK IN CONJUNCTION
WITH A BROOKS LOCK GUARD #865 OR
#86505, WITH A PERMANENTLY WELDED
BRACKET.

Bottom View



METER SKT-(1) 200A 600V 3P4W G90 N3R 7-TERM LARGE HUB
OPNG TPLX GRD LEVER BYP AEP BARREL LK TOP/BOT FEED

CAT NO	DWG DATE	REV #
UFTH7213TMEP	04/25/2016	02