




Left Side View



Front View Interior




Right Side View



Notes

- 1) FINISH: GRAY
- 2) CABINET: BACK IS FABRICATED FROM 14 GA GALV. STEEL. TOP, BOTTOM, & FRONT IS FABRICATED FROM 16 GA GALV. STEEL.
- 3) 320 AMP CONTINUOUS 600 VAC, 3 PHASE, 4-WIRE 320 AMP BYPASS
- 4) FOR BROOKS OR INTER-TITE STANDARD LENGTH BARREL LOCK IN CONJUNCTION WITH BROOKS LOCK GUARDS #865 OR #86505, WITH PERMANENTLY WELDED BRACKET.
- 5) MIDWEST LABEL ATTACHED TO THE END OF CARTON.
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED.
- 7) MIDWEST LOGO STAMPED IN THE LOWER LEFT-HAND CORNER OF FRONT.

Bottom View



METER SKT-(1) 320A 600V 3P4W G90 N3R 7-TERM LARGE HUB OPNG TPLX GRD LEVER BYP AEP BARREL LK TOP/BOT FEED

CAT NO	DWG DATE	REV #
UFTH7336TMEP	06/22/2016	01