




### Front View

### Side View




### Neutral Stud Detail



### Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV STEEL
- 3) 320 AMP CONTINUOUS, 600 VAC, 1 PHASE, 3 WIRE, 320 AMP BYPASS
- 4) INHIBITOR APPLIED TO THE CONNECTORS
- 5) GE LABEL ATTACHED TO THE END OF THE CARTON
- 6) TEMPORARY CARDBOARD METER OPENING COVER PROVIDED
- 7) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF THE FRONT

### Bottom View



METER SKT-(1) 320A 600V 1P3W G90 4-TERM N3R  
 LARGE HUB OPNG (2) TPLX GRD LEVER BYP TOP FEED

CAT NO	DWG DATE	REV #
UH43068TCPLGE	02/10/2016	01