



Left Side View




Front View Interior



Notes

- 1) FINISH: GRAY
- 2) CABINET: 16 GA GALV. STEEL
- 3) 200 AMP CONTINUOUS PER POSITION
600VAC, 1 PHASE, 3-WIRE
360 AMP CONTINUOUS (TOTAL) UNIT RATING WITH CU
310 AMP CONTINUOUS (TOTAL) UNIT RATING WITH AL
- 4) TEMPORARY CARDBOARD
METER OPENING COVER PROVIDED
- 5) GE LABEL ATTACHED TO THE END OF THE CARTON
- 6) GE LOGO LOCATED IN THE LOWER LEFT-HAND
CORNER OF THE FRONT

Bottom View



HORIZ GANGED METER SKT-(4) 200A 600V 1P3W G90 N3R 4-TERM
LARGE HUB OPNG CENTER FEED HORN BYP TRIPLEX GRD

CAT NO	DWG DATE	REV #
UHT4R2352TGE	04/15/2016	02