




Left Side View




Front View Interior



Front View Exterior




Right Side View




Notes

- 1) CABINET CONSTRUCTED FROM 16 GAUGE GALVANIZED STEEL
- 2) FINISH: GREY
- 3) UNIT RATING: 20 AMP CONTINUOUS 600VAC 3 PHASE 4 WIRE
- 4) TEST SWITCH INSTALLED
- 5) UNIT IS NOT FACTORY WIRED
- 6) UNIT IS SUPPLIED WITH TEMPORARY CARDBOARD METER OPENING COVER
- 7) GE LABEL ATTACHED TO END OF THE CARTON
- 8) GE LOGO STAMPED ON LOWER LEFT HAND CORNER OF FRONT
- 9) SAFETY LABEL IS LOCATED ON THE LOWER RIGHT-HAND CORNER OF THE FRONT
- 10) FOR FP&L USE ONLY

Bottom View



GE is a registered trademark used under license from General Electric company.

		
TRANSFORMER RATED MTR – 20A 13T 3P4W N3R STEEL SMALL HUB CVR PLT TOP/BOT FEED FP&L APPROVED		
CAT NO	DWG DATE	REV #
USTH131C758GE	02/09/2017	01