



Modular Metering Renewal Parts

Mini Mod* III
Meter Mod* III



Modular Metering Renewal Parts

Mini Mod III Renewal Parts

Mini Mod III Catalog Number	Part Catalog Number					
	Utility Pull Section Cover	Wireway Cover	Meter Socket Assembly	Meter Cover	Endwall with KO's	Endwall without KO's
TMM2212R, TMM2212RF	TMM2122UCVR	TMMCCVR01	—	TMC12 ⁴	TMEW10	TMEWNBK10
TMM4312R, TMM4312RF	TMM1234UCVR	TMMCCVR04	TMMSA1	TMC12 ⁴	TMEW11	TMEWNBK11
TMM4412R, TMM4412RF	TMM1234UCVR	TMMCCVR05	TMMSA1	TMC12	TMEW11	TMEWNBK11
TMM6512R, TMM6512RF	TMM1256UCVR	TMMCCVR02 ¹	TMMSA1	TMC12 ⁴	TMEW12	TMEWNBK12
TMM6612R	TMM1256UCVR	TMMCCVR03 ¹	TMMSA1	TMC12 ⁴	TMEW12	TMEWNBK12
TMM4220R	TMM202UCVR	TMMCCVR19	TMMSA1	TMC20 ⁴	TMEW13	TMEWNBK13
TMM6320R, TMM6320RF	TMMR2034UCVR	TMMCCVR09	TMMSA1	TMC20	TMEW13	TMEWNBK13
TMM6420R, TMM6420RF	TMMR2034UCVR	TMMCCVR10	TMMSA1	TMC20	TMEW13	TMEWNBK13
TMM6520R	TMM2056UCVR	TMMCCVR07 ²	TMMSA1	TMC20	TMEW14	TMEWNBK14
TMM6620R	TMM2066UCVR	TMMCCVR08 ²	TMMSA1	TMC20	TMEW14	TMEWNBK14
TMMR2212R, TMMR2212RF, TMMR2212RHB	—	TMMCCVR21	—	TMCR12 ⁴	TMEW10	TMEWNBK10
TMMR4312R, TMMR4312RF, TMMR4312RHB	TMM1234UCVR	TMMCCVR13	TMMSA1 ³	TMCR12 ⁴	TMEW11	TMEWNBK11
TMMR4412R, TMMR4412RF, TMMR4412RHB	TMM1234UCVR	TMMCCVR14	TMMSA1 ³	TMCR12	TMEW11	TMEWNBK11
TMMR6512R, TMMR6512RF, TMMR6512RHB	TMM1256UCVR	TMMCCVR11 ¹	TMMSA1 ³	TMCR12 ⁴	TMEW12	TMEWNBK12
TMMR6612R, TMMR6612RF, TMMR6612RHB	TMM1256UCVR	TMMCCVR12 ¹	TMMSA1 ³	TMCR12 ⁴	TMEW12	TMEWNBK12
TMMR4420R, TMMR4420RF, TMMR4420RHB	TMM202UCVR	TMMCCVR20	TMMSA1 ³	TMCR20 ⁴	TMEW13	TMEWNBK13
TMMR6320R, TMMR6320RF, TMMR6320RHB	TMMR2034UCVR	TMMCCVR17	TMMSA1 ³	TMCR20	TMEW13	TMEWNBK13
TMMR6420R, TMMR6420RF, TMMR6420RHB	TMMR2034UCVR	TMMCCVR18	TMMSA1 ³	TMCR20	TMEW13	TMEWNBK13
TMMR6520R, TMMR6520RF, TMMR6520RHB	TMM2056UCVR	TMMCCVR15 ²	TMMSA1 ³	TMCR20	TMEW14	TMEWNBK14
TMMR6620R, TMMR6620RF, TMMR6620RHB	TMM2056UCVR	TMMCCVR16 ²	TMMSA1 ³	TMCR20	TMEW14	TMEWNBK14

¹For center wireway cover, order TMMCENCVR1.

²For center wireway cover, order TMMCENCVR2.


³For ringless style units with horn bypass, all replacement parts are the same except for the meter socket assembly. Order part number TMMSB instead of TMMSA1 for ringless with horn bypass.T

⁴Top position meter socket cover, add "T" to part number suffix. Example: TMCR12 would be ordered as TMCR12T for top position meter socket cover.

Mini Mod III Renewal Parts

Part	125 Amp	200 Amp
Breaker Cover	TMBC12	TMBC20
KO Plate	TMKPB12	TMKPB20
Hardware	TMMSK	TMMSK
Bonding Strap	TMMBSK	TMMBSK

Mini Mod III Modular Metering



Modular Metering Renewal Parts

Mini Mod III Tenant Main Circuit Breakers

Tenant Main Breakers for 125A, 2 Pole Sockets

Amps	10kAIC	22kAIC	Wire Size
60	THQL2160	THHQL2160	(1) #8-#3 CU; #8-#3 AL
70	THQL2170	THHQL2170	(1) #6-1/0 CU; #4-#1/0 AL
80	THQL2180	THHQL2180	
90	THQL2190	THHQL2190	
100	THQL21100	THHQL21100	(1) #2-2/0 CU; #2-2/0 AL
110	THQL21110	THHQL21110	—
125	THQL21125	THHQL21125	(1) #2-2/0 CU; #2-2/0 AL
125	THQL21125SSF ¹	—	—

¹Sub-Feed lug. No overcurrent protection

Tenant Main Breakers for 125A, 2 Pole Sockets

Amps	QL 42 kAIC	Wire Size
60	TMQL2160	#8-#1 (Cu) or #8-1/0 (Al)
70	TMQL2170	
80	TMQL2180	
90	TMQL2190	
100	TMQL21100	
125	TMQL21125	2/0 - #14

Tenant Main Breakers for 200A, 2 Pole Sockets

Amps	10kAIC	22kAIC	Wire Size
100	TQD22100	THQD22100	(1) #1-300 CU; #1-300 AL
125	TQD22125	THQD22125	
150	TQD22150	THQD22150	
175	TQD22175	THQD22175	
200	TQD22200	THQD22200	

Tenant Main Circuit Breakers for 200A, 2 Pole Sockets

Amps	QD Old Catalog No. - Obsolete. Replaced by QV.	QV 100 kAIC New Catalog No.	Wire Size
60	—	TMQV22060MM	#14-1/0 only
70	TMQD22070	TMQV22070MM	#4-4/0 only
80	TMQD22080	TMQV22080MM	
90	TMQD22090	TMQV22090MM	
100	TMQD22100	TMQV22100MM	
110	—	TMQV22110MM	
125	TMQD22125	TMQV22125MM	
150	TMQD22150	TMQV22150MM	std = #4-4/0 ²
175	TMQD22175	TMQV22175MM	
200	TMQD22200	TMQV22200MM	

²For 175A-200A use TMQV225L2 for 2 Pole.

Modular Metering Renewal Parts

Mini Mod III Field Installed Accessories


Bypass Kits

Description	Catalog No.	
Manual Slider-Type (Ring Type Only) ¹	125A top socket for 2 & 3 gang	TMBPM12TA
	125A for all other sockets	TMBPM12A
	200A for top position	TMBPM20TA
	200A for all other sockets	TMBPM20A
Jumper Straps Type (use with TMCA)	TMBPJ20 ³	
Cover, Including Jumper Strap Type — fits all (Ring Type & Ringless) ²	TMBPC20 ³	
Horn-Type — fits all (Ringless Only) ¹	TMBPH20A	


¹100A continuous

²200A continuous

³Not UL Listed



TMBPM12TA



TMBPJ20



TMBPC20

Semi-Flush Kits

Socket Rating	Description	Catalog No.
125A Sockets	2 gang	TMM12SF2
	3 and 4 gang	TMM12SF4
	5 and 6 gang	TMM12SF6
200A Sockets	3 and 4 gang	TMM20SF4
	5 and 6 gang	TMM20SF6



TMM12SF2



TMM20SF4

Fifth Jaw Kits

Description	Catalog No.
Bused; 3, 6 or 9 o'clock mounting. Not suitable for 2-gang because neutral bus not available.	TM5JA
Isolated; 3 or 9 o'clock mounting only. Suitable for all meter stacks	TM5JUA

Compression Lug Landing Kit

Description	Catalog No.
600 amp	TMM6CLL

Includes 3 pads each with 2 threaded stud connections (and hardware) for compression or mechanical lugs with NEMA 2-hole bolt configuration (lugs not furnished). Not suitable for 2-gang.

Modular Metering Renewal Parts


Mini Mod III

Field Installed Accessories (continued)


Steel Meter Socket Covers

Description		Catalog No.
Blank (fits bottom position only)	125 Amp	TMCB12B
	200 Amp	TMCB20B
Ringless (Field -converts ring-type to ringless) ¹	125 amp top socket for 2 and 3 gang	TMCR12T
	125 amp for all other sockets	TMCR12
	200 amp for all sockets	TMCR20


¹Conversion from ringless to ring type is not possible. No conversion kit available



TMCB12B



TMCR12T



TMCR12

Sealing Rings

Description	Material	Catalog No.
Screw Type	Aluminum	TSR1
Snap Type	Stainless Steel	TSR3
Screw and Lock Type	Aluminum	TSR4
Snap Type	Aluminum (Standard)	TSR5



TSR1



TSR3




TSR4



TSR5

Miscellaneous


Description	Catalog No.
Lexan® Meter Socket Cover Plate (without tabs)	TMCA
Lexan® Meter Socket Cover Plate	TMCP
Equipment Ground Bar, (6) 6-2/0	TMEG
Individual Meter Socket Barrier Kit (includes 6)	TMBR
Mounting Z-Rail, 4-foot	TMZR
Lug Kit for (3) 4/0 cable	TMPAL40



TMCA



TMCP



TMBR



TMPAL40



TMZR

Modular Metering Renewal Parts

Bus Caps for Meter Mod III¹

Description	Catalog Number
End Cap (right/deep)	TMECR
End Cap (left/flat)	TMECL

¹ Shipped with main modules. Not shipped with meter stack modules, but may be installed on them.

Main Lug Module Renewal Parts

Catalog Number	Front Cover	Drip Hood	Endwall with KO's	Endwall without KO's
TMPL8R	TMPFCB	TMDH9	TMEW1	TMEWNKO1
TMPL12R	TMPFCB	TMDH9	TMEW1	TMEWNKO1
TMP3L4R	TMP3LC6	N/A	N/A	N/A
TMP3L6R	TMP3LC6	N/A	N/A	N/A
TMP3L8R	TMPFCB	TMDH9	TMEW1	TMEWNKO1
TMP3L12R	TMPFCB	TMDH9	TMEW1	TMEWNKO1

Main Lug Module - Lug Options (for 800A & 1200A)

Lug	Description	Wire Range	Catalog Number
Standard	Set of 3 (per phase)	1/0 - 750kcmil	TMPL750
Alternate	Single lug (Use 2 lugs per phase or neutral)	(2) 200-500 kcmil	TMPAL30

Compression Lug Landing Kits (NEMA 2-hole spacing) for 3-Phase Main Lug Modules

Rating	Stud Sets per Phase and Neutral	Catalog Number
400A	1	TMP3L6CLL
600A	1	TMP3L6CLL
800A	2	TMP3L12CLL1
1200A	2	TMP3L12CLL1


Main Circuit Breaker Module Renewal Parts

Catalog Number	Main Breaker	Front Cover	Drip Hood	Main Cover	Endwall with KO's	Endwall without KO's
TMPSB4R	SGHA26AT0400	TMPFCVR1	TMDH9	TMBC40	TMEW1	TMEWNKO1
TMPSHB4R	SGLA26AT0400					
TMPSB6R	SGHA26AT0600					
TMPSB8R	SKHA26AT0800	TMPFCVR2				
TMPSB10R	SKHA26AT1200					
TMPSB12R						
TMP3SB4R	SGHA36AT0400	TMPFCVR1				
TMP3SHB4R	SGLA36AT0400					
TMP3SB6R	SGHA36AT0600					
TMP3SB8R	SKHA36AT0800	TMPFCVR2				
TMP3SB10R	SKHA36AT1200					
TMP3SB12R						

Alternate Rating Plugs, Field Installed for Spectra Main Breakers

Main Ampere Rating of Breaker	Alternate Rating	Rating Plug Catalog Number
400	225	SRPG400A225
	250	SRPG400A250
	300	SRPG400A300
	350	SRPG400A350
600	400	SRPG600A400
	450	SRPG600A450
	500	SRPG600A500
800	600	SRPK800A600
	700	SRPK800A700
1000	800	SRPK1200A800
1200	1000	SRPK1200A1000


Main Lug Module



Shunt Trip, Field Installed

Type	Catalog Number
120Vac Shunt Trip	SAST1
240Vac Shunt Trip	SAST2

Modular Metering Renewal Parts



Main Switch Module Renewal Parts

Catalog Number	Front Cover	Drip Hood	Endwall with KO's	Endwall without KO's	Switch Handle
TMPFB4R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB6R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB8R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB12RT	TMPFCB1	TMDH17	TMEW2	TMEWnk02	N/A
TMP3FB4R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FB6R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FB8R	TMPFCB	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FB12RT	TMPFCB1	TMDH17	TMEW2	TMEWnk02	N/A
TMPFT4R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFT6R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFT8R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FT4R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FT6R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FT8R	TMPFCT	TMDH9	TMEW1	TMEWnk01	TMPFSH

Alternate Lug Kit for 400A & 600A Main Switch Modules

Description	Catalog Number
Accepts (4) 3/0-750 mcm for use with 400 and 600A switch	TMPL40

Main Switch Module with Integral Pull Box

Catalog Number	Front Cover	Pull Box Cover	Drip Hood	Endwall with KO's	Endwall without KO's	Switch Handle
TMPFB4RCLL	TMPFCCLL	TMPFPBC	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB6RCLL	TMPFCCLL	TMPFPBC	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB8RCLL	TMPFCCLL	TMPFPBC	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMPFB12RCLLT	TMPFCCLLF3	TMPFPBC1	TMDH17	TMEW2	TMEWnk02	N/A
TMP3FB4RCLL	TMPFCCLL	TMPFPBC	TMDH9	TMEW1	TMEWnk01	TMPFSH
TMP3FB6RCLL	TMPFCCLLF1	TMPFPBCP	TMDH16	TMEW4	TMEWnk04	TMPFSH
TMP3FB8RCLL	TMPFCCLLF2	TMPFPBCP	TMDH16	TMEW4	TMEWnk04	TMPFSH
TMP3FB12RCLLT	TMPFCCLLF3	TMPFPBC1	TMDH17	TMEW2	TMEWnk02	N/A

Class T Fuses for Main Switch Modules


Frame Size	Ampere Rating	Catalog Number
400	250	TFUSE250
	300	TFUSE300
	350	TFUSE350
	400	TFUSE400
600	500	TFUSE500
	600	TFUSE600
800	800	TFUSE800

Main Pull Box Renewal Parts

Catalog Number	Front Cover / Pull Box Cover	Drip Hood	Endwall
TMPU4R	TMP3U4	TMDH13	1
TMPU8R	—	TMDH14	1
TMPU12R	—	TMDH15	1
TMP3U4R	—	TMDH13	1
TMP3U8R	—	TMDH14	1
TMP3U12R	—	TMDH15	1

¹No endwalls available for Main Pullbox units as the enclosure is welded.

Residential Metering



Single-Phase Meter Stack Module Renewal Parts

Catalog Number	Wireway Cover	Meter Socket Assembly	Tenant Breaker Cover	Meter Cover	Drip Hood	Endwall with KO's NEMA 3R ⁵	Endwall without KO's NEMA 3R ⁵
TMP8212R, TMP8212RF	TMPCCVR01	TMMSA1	TMBC12	TMC12 ³	TMDH11	TMEW6	TMEWNK06
TMP8312R, TMP8312RF	TMPCCVR03	TMMSA1	TMBC12	TMC12 ³	TMDH11	TMEW6	TMEWNK06
TMP8412R, TMP8412RF	TMPCCVR05	TMMSA1	TMBC12	TMC12	TMDH11	TMEW6	TMEWNK06
TMP8512R, TMP8512RF	TMPCCVR13	TMMSA1	TMBC12	TMC12	TMDH11	TMEW6	TMEWNK06
TMP8612R, TMP8612RF	TMPCCVR15	TMMSA1	TMBC12	TMC12	TMDH11	TMEW6	TMEWNK06
TMP8220R	TMPCCVR07	TMMSA1	TMBC20	TMC20	TMDH12	TMEW7	TMEWNK07
TMP8320R, TMP8320RF	TMPCCVR09	TMMSA1	TMBC20	TMC20	TMDH12	TMEW7	TMEWNK07
TMP8420R, TMP8420RF	TMPCCVR11	TMMSA1	TMBC20	TMC20	TMDH12	TMEW7	TMEWNK07
TMPS8212R ² , TMPS8212RF, TMPS8212RH, TMPS8212RHBF	TMPCCVR02	TMMSA1 ²	TMBC12	TMCR12 ⁴	TMDH11	TMEW6	TMEWNK06
TMPS8312R ² , TMPS8312RF, TMPS8312RH, TMPS8312RHBF	TMPCCVR04	TMMSA1 ²	TMBC12	TMCR12 ⁴	TMDH11	TMEW6	TMEWNK06
TMPS8412R ² , TMPS8412RF, TMPS8412RH, TMPS8412RHBF	TMPCCVR06	TMMSA1 ²	TMBC12	TMCR12	TMDH11	TMEW6	TMEWNK06
TMPS8512R ² , TMPS8512RF, TMPS8512RH	TMPCCVR14	TMMSA1 ²	TMBC12	TMCR12	TMDH11	TMEW6	TMEWNK06
TMPS8612R ² , TMPS8612RF, TMPS8612RH	TMPCCVR16	TMMSA1 ²	TMBC12	TMCR12	TMDH11	TMEW6	TMEWNK06
TMPS8220R ² , TMPS8220RF, TMPS8220RH	TMPCCVR08	TMMSA1 ²	TMBC20	TMCR20	TMDH12	TMEW7	TMEWNK07
TMPS8320R ² , TMPS8320RF, TMPS8320RH	TMPCCVR10	TMMSA1 ²	TMBC20	TMCR20	TMDH12	TMEW7	TMEWNK07
TMPS8420R ² , TMPS8420RF, TMPS8420RH, TMPS8420RHBF	TMPCCVR12	TMMSA1 ²	TMBC20	TMCR20	TMDH12	TMEW7	TMEWNK07

²For ringless style units with horn bypass, all replacement parts are the same except for the meter socket assembly. Order part number TMMSB instead of TMMSA1 for ringless with horn bypass.

³For top position, use meter socket cover TMC12T.

⁴For top position, use meter socket cover TMCR12T.

⁵For NEMA 1 painted top endwalls, see next page.

Modular Metering Renewal Parts

Mini Mod III Field Installed Accessories


Bypass Kits

Description		Catalog No.
Manual Slider-Type (Ring Type Only) ¹	125A top socket for 2 & 3 gang	TMBPM12TA
	125A for all other sockets	TMBPM12A
	200A for top position	TMBPM20TA
	200A for all other sockets	TMBPM20A
Jumper Straps Type (use with TMCA)		TMBPJ20 ³
Cover, Including Jumper Strap Type — fits all (Ring Type & Ringless) ²		TMBPC20 ³
Horn-Type — fits all (Ringless Only) ¹		TMBPH20A

¹100A continuous

²200A continuous

³Not UL Listed



TMBPM12TA



TMBPJ20



TMBPC20


Fifth Jaw Kits

Description	Catalog No.
Bused; 3, 6 or 9 o'clock mounting. Not suitable for 2-gang because neutral bus not available.	TM5JA


Steel Meter Socket Covers

Description	Catalog No.	
Blank (fits bottom position only)	125A	TMCB12B
	200A	TMCB20B
Ringless (Field -converts ring-type to ringless) ⁴	125A top socket for 2, 5 & 6 gang	TMCR12T
	125A for all other sockets	TMCR12
	200A for all sockets	TMCR20


⁴Conversion from ringless to ring type is not possible. No conversion kit available



TMCB12B



TMCR12T



TMCR12

Modular Metering Renewal Parts

Mini Mod III Field Installed Accessories


Sealing Rings

Description	Material	Catalog No.
Screw Type	Aluminum	TSR1
Snap Type	Stainless Steel	TSR3
Screw and Lock Type	Aluminum	TSR4
Snap Type	Aluminum (Standard)	TSR5



Miscellaneous

Description	Catalog No.
Lexan® Meter Socket Cover Plate (without tabs)	TMCA
Lexan® Meter Socket Cover Plate	TMCP
Equipment Ground Bar, (6) 6-2/0	TMEG
Individual Meter Socket Barrier Kit (includes 6)	TMBR
Mounting Z-Rail, 4-foot	TMZR
Spacer, 4-inch, 4 Cross Bar Rated, 1200A	TMPS12
Elbow, 16" x 16", 4 Cross Bus Rated 1200A	TMPE12
Elbow, 12" x 12", 4 Cross Bus Rated 1200A	TMPE12A



Modular Metering Renewal Parts


Three-Phase Commercial Meter Stack Module Renewal Parts

Catalog Number	Wireway Cover	Meter Socket Assembly	Tenant Breaker Cover	Meter Cover	Drip Hood	Endwall with KO's	Endwall without KO's
TMPR312122R	TMPRCCVR05	TMMSA3	TMBC20	TMCR322A	—	²	TMEWNK08
TMPR312140TR	TMPRCCVR09	TMMSA3	TMBC20	TMCR322A	—	²	TMEWNK08
TMPR312222R	TMPRCCVR06	TMMSA3	TMBC20	TMCR322A	—	²	TMEWNK08
TMPR312322R	TMPRCCVR07	TMMSA3	TMBC20	TMCR322A	—	²	TMEWNK08
TMPR312422R	TMPRCCVR08	TMMSA3	TMBC20	TMCR322A	—	²	TMEWNK09
TMP38120RT	TMPRCCVR19	TMMSA5	TMBC20	TMCR320E	¹	²	¹
TMP312220RT	TMPRCCVR20	TMMSA5	TMBC20	TMCR320E	¹	²	¹
TMP312320RT	TMPRCCVR21	TMMSA5	TMBC20	TMCR320E	¹	²	¹

¹Not available as enclosure is welded.

²Not available as commercial metering does not offer an endwall with knockouts.

Commercial Metering



Main Tenant Breaker Accessories

Description	Catalog Number
TQD Mounting Kit – 2 Pole	TMTQD2
TQD Mounting Kit – 3 Pole	TMTQD3
TMQD Load Lug: 60 – 90A	TCAL20
TMQD Load Lug: 100 – 150A	TCAL21
TMQD Load Lug: 175 – 225A	TCAL22

Single-Phase Commercial Metering Renewal Parts

Catalog Number	Wireway Cover	Meter Socket Assembly	Tenant Breaker Cover	Meter Cover	Drip Hood	Endwall with KO's	Endwall without KO's
TMP8120RTAB	TMPRCCVR10	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP8120RTAC	TMPRCCVR11	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP8120RTBC	TMPRCCVR12	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112220RTAB	TMPRCCVR13	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112220RTAC	TMPRCCVR14	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112220RTBC	TMPRCCVR15	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112320RTAB	TMPRCCVR16	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112320RTAC	TMPRCCVR17	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMP112320RTBC	TMPRCCVR18	TMMSA4	TMBC20	TMCR320E	¹	²	¹
TMPR12122R	TMPRCCVR01	TMMSA2	TMBC20	—	—	²	TMEWNK08
TMPR12222R	TMPRCCVR02	TMMSA2	TMBC20	—	—	²	TMEWNK08
TMPR12322R	TMPRCCVR03	TMMSA2	TMBC20	—	—	²	TMEWNK08
TMPR12422R	TMPRCCVR04	TMMSA2	TMBC20	—	—	²	TMEWNK09

¹Not available as enclosure is welded.

²Not available as commercial metering does not offer an endwall with knockouts.

Modular Metering Renewal Parts

Tenant Main Circuit Breakers for 1PH Residential Meter Modules (800 & 1200A Horizontal Bussing)

Tenant Main Breakers for 125A, 2 Pole Sockets

Amps	10kAIC	22kAIC	Wire Size
60	THQL2160	THHQL2160	(1) #8-#3 CU; #8-#3 AL
70	THQL2170	THHQL2170	(1) #6-1/0 CU; #4-#1/0 AL
80	THQL2180	THHQL2180	
90	THQL2190	THHQL2190	
100	THQL21100	THHQL21100	(1) #2-2/0 CU; #2-2/0 AL
110	THQL21110	THHQL21110	—
125	THQL21125	THHQL21125	(1) #2-2/0 CU; #2-2/0 AL
125	THQL21125SF ¹	—	—

¹Sub-Feed lug. No overcurrent protection.

Tenant Main Breakers for 125A, 2 Pole Sockets

Amps	QL 42 kAIC	Wire Size
60	TMQL2160	#8-#1 (Cu) or #8-1/0 (Al)
70	TMQL2170	
80	TMQL2180	
90	TMQL2190	
100	TMQL21100	
125	TMQL21125	2/0 - #14

Tenant Main Breakers for 200A, 2 Pole Sockets

Amps	10kAIC	22kAIC	Wire Size
100	TQD22100	THQD22100	(1) #1-300 CU; #1-300 AL
125	TQD22125	THQD22125	
150	TQD22150	THQD22150	
175	TQD22175	THQD22175	
200	TQD22200	THQD22200	

Tenant Main Circuit Breakers for 200A, 2 Pole Sockets

Amps	QD Old Catalog No. - Obsolete. Replaced by QV.	QV 100 kAIC New Catalog No.	Wire Size
60	—	TMQV22060MM	#14-1/0 only
70	TMQD22070	TMQV22070MM	#4-4/0 only
80	TMQD22080	TMQV22080MM	
90	TMQD22090	TMQV22090MM	
100	TMQD22100	TMQV22100MM	
110	—	TMQV22110MM	
125	TMQD22125	TMQV22125MM	
150	TMQD22150	TMQV22150MM	std = #4-4/0 ²
175	TMQD22175	TMQV22175MM	
200	TMQD22200	TMQV22200MM	

²For 175A-200A use TMQV225L2 for 2 Pole

Modular Metering Renewal Parts

Tenant Main Circuit Breakers for 1PH Commercial Meter Stack Modules (1200A Horizontal Bussing)

Tenant Main Circuit Breakers for 225A, 2 Pole Sockets

Amps	10kAIC	Wire Size
15	TEB122015	(1) #14-3 CU; #12-1 AL
20	TEB122020	
25	TEB122025	
30	TEB122030	
35	TEB122035	
40	TEB122040	
45	TEB122045	
50	TEB122050	
60	TEB122060	
70	TEB122070	
80	TEB122080	
90	TEB122090	
100	TQD22100	(1) #1-300 CU; #1-300 AL
125	TQD22125	
150	TQD22150	
175	TQD22175	
200	TQD22200	
225	Use TMQV	

Tenant Main Circuit Breakers for 225A, 2 Pole Sockets

Amps	22kAIC	Wire Size
100	THQD22100	(1) #1-300 CU; #1-300 AL
125	THQD22125	
150	THQD22150	
175	THQD22175	
200	THQD22200	
225	Use TMQV	

Tenant Main Circuit Breakers for 200A/225A, 2 Pole Sockets

Amps	QD Old Catalog No. - Obsolete. Replaced by QV.	QV 100 kAIC New Catalog No.	Wire Size
60	—	TMQV22060MM	#14-1/0 only
70	TMQD22070	TMQV22070MM	#4-4/0 only
80	TMQD22080	TMQV22080MM	
90	TMQD22090	TMQV22090MM	
100	TMQD22100	TMQV22100MM	
110	—	TMQV22110MM	
125	TMQD22125	TMQV22125MM	
150	TMQD22150	TMQV22150MM	
175	TMQD22175	TMQV22175MM	std = #4-4/0 ¹
200	TMQD22200	TMQV22200MM	
225	TMQD22225	TMQV22225MM	

¹For 175A-200A use TMQV2225L2 to get 300MCM terminals.

Modular Metering Renewal Parts

Tenant Main Circuit Breakers for 3PH Commercial Meter Stack Modules (1200A Horizontal Bussing)

Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	10kAIC	Wire Size
15	TEB132015	(1) #14-3 CU; #12-1 AL
20	TEB132020	
25	TEB132025	
30	TEB132030	
35	TEB132035	
40	TEB132040	
45	TEB132045	(1) #6/20 CU; #4-2/0 AL
50	TEB132050	
60	TEB132060	
70	TEB132070	(1) #3-3/0 CU; #1-3/0 AL
80	TEB132080	
90	TEB132090	
100	TEB132100	(1) #1-300 CU; #1-300 AL
125	TQD32125	
150	TQD32150	
175	TQD32175	
200	TQD32200	
225	Use TMQV	

Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	22kAIC	Wire Size
100	THQD32100	(1) #1-300 CU; #1-300 AL
125	THQD32125	
150	THQD32150	
175	THQD32175	
200	THQD32200	
225	Use TMQV	

Tenant Main Circuit Breakers for 200A/225A, 3 Pole Sockets

Amps	QD Old Catalog No. - Obsolete. Replaced by QV.	QV 100 kAIC New Catalog NO.	Wire Size
60	—	TMQV32060	#14-1/0 only
70	TMQD32070	TMQV32070	#4-4/0 only
80	TMQD32080	TMQV32080	
90	TMQD32090	TMQV32090	
100	TMQD32100	TMQV32100	
110	—	TMQV32110	
125	TMQD32125	TMQV32125	
150	TMQD32150	TMQV32150	std = #4-4/0 ¹
175	TMQD32175	TMQV32175	
200	TMQD32200	TMQV32200	
225	TMQD32225	TMQV32225	

¹For 175A-200A use TMQV225L2 to get 300MCM terminals.

Modular Metering Renewal Parts


Commercial Meter Stack Module Accessories

Description	Catalog Number
TEB Breaker Mounting Kit	TMTEB
Barrel Lock Bracket and Guard Kit	TMBL
Totalizing Jumper Type Bypass Kit ¹	TMBPT320 ²
Blank Meter Socket Cover-Steel, Fits All Positions	TMCB322A
Replacement Phase Balancing Jumper Kit ²	TMPJ31
Individual Meter Socket Barrier Kit (includes 6)	TMBR3
Insulator for Lever Bypass Handle	TMHN
Mounting Z Rail, 4-Foot	TMZR
Spacer, 4-inch, 4 Cross Bus Rated 1200 amps	TMPS12
Elbow, 16" x 16", 4 Cross Bus Rated 1200A ³	TMPE12
Elbow, 12" x 12", 4 Cross Bus Rated 1200A ³	TMPE12A

¹180A continuous

²Not UL Listed

³Indoor, Type 1



TMTEB




TMHN




TMBL



TMCB322A



TMBPT320



TMBR3

NEMA 1 Painted Top Endwalls

Type	125 Amp	200 Amp
With KO's	TM12N1WLK	TM20N1WLK
Without KO's	TM12N1WL	TM20N1WL

Miscellaneous Parts

Description	Catalog Number
Phase Balancing Kit, Single Phase Commercial Metering	35MMPHBALKIT
Mounting Kit, Meter Mod III - Residential Units	99-4172-2
Bracket Kit - All Breakers and Fusible Mains	99-4183-2

GE
41 Woodford Avenue
Plainville, CT 06062
1-800-431-7867
www.geindustrial.com

*Indicates a trademark of the General Electric Company and/or its affiliates.
Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, express or implied, that such performance will be obtained under end-use conditions.
©2018, General Electric Company and/or its affiliates. All rights reserved.

3.18 DET388D