



NOTE:
 1. ALL DIMENSIONS ARE IN INCHES.
 2. ALL DIMENSIONS HAVE ± 0.125 TOLERANCE.
 3. KNOCKOUTS NO. 1 THRU 4 ARE TANGENTIAL.
 4. KNOCKOUTS NO. 5, 6, & 7 ARE CONCENTRIC.
 5. KNOCKOUTS OMITTED IN TOP ENDWALL, TOP BACKWALL, AND TOP SIDEWALLS FOR CATALOGS TC35361R, TDT3361R AND TDT3362R.

DIMENSION TABLE

GCAT NO.	DESCRIPTION	A	B	C	CONDUIT KNOCKOUTS QUANTITY AND SIZE						
					1	2	3	4	5	6	7
TDT3362R	60A 3P DBL THR N3R 600V FUSIBLE	37.02	33.50	36.62	(1) 1/2-3/4-1	(1) 3/4-1-11/4	(1) 1-11/4-1-1/2	(1) 1 1/4-1-1/2-2	(1) 1/2-3/4-1-11/4	(1) 3/4-1-11/4-1-1/2	(1) 1-11/4-1-1/2-2
TDT3361R	30A 3P DBL THR N3R 600V FUSIBLE	25.02	21.50	24.62	(1) 1/2-3/4-1	(1) 3/4-1-11/4	(1) 1-11/4-1-1/2	(1) 1 1/4-1-1/2-2	(1) 1/2-3/4-1-11/4	(1) 3/4-1-11/4-1-1/2	(1) 1-11/4-1-1/2-2
TC35361R	30A 3P DBL THR N3R 600V NONFUSE	25.02	21.50	24.62	(1) 1/2-3/4-1	(1) 3/4-1-11/4	(1) 1-11/4-1-1/2	(1) 1 1/4-1-1/2-2	(1) 1/2-3/4-1-11/4	(1) 3/4-1-11/4-1-1/2	(1) 1-11/4-1-1/2-2
TC35361	30A 3P DBL THR N1 600V NONFUSE	25.02	21.50	24.62	(2) 1/2-3/4-1	(2) 3/4-1-11/4	(2) 1-11/4-1-1/2	(2) 1 1/4-1-1/2-2	(2) 1/2-3/4-1-11/4	(2) 3/4-1-11/4-1-1/2	(2) 1-11/4-1-1/2-2

Industrial Solutions by ABB

OUTLINE DRAWING - DOUBLE THROW SAFETY SWITCH
30- 60A

THIRD ANGLE	SHEET#	DWG NO.	DATE	REV
	1 of 1	10103091SH185	10/19	02