



MEG Approved Meter Socket Load Centers

The meter socket load centers in this publication meet Meter Equipment Group (MEG) requirements.

The utility group called Meter Equipment Group (MEG) consists of the following utilities:

- Florida Power & Light (Florida)
- Tampa Electric (Florida)
- Gulf Power (Florida)
- Oklahoma Gas & Electric (Oklahoma)
- Duke Energy (Florida, North and South Carolina, Indiana, Ohio and Kentucky)



MEG Approved Meter Socket Load Centers

Main Ampere Rating	1 Pole, 1" Spaces	2 Pole, 1" Spaces	1 Pole, 1/2" Spaces	2 Pole, 1/2" Spaces	Total 1 Pole Spaces	Product Number	Socket Type	Enclosure	Feed-Thru Lugs	Front Type	Bypass Type	Bussing Type	UL Incoming	Agency Certification
--------------------	-------------------	-------------------	---------------------	---------------------	---------------------	----------------	-------------	-----------	----------------	------------	-------------	--------------	-------------	----------------------

Main Breaker / Ringless / Single-Phase, 3 Wire, 120/240 Vac with Bonded Neutrals

150	4	2	8	3	8	TSMR415CSFLFMG	Ringless	Outdoor (NEMA 3R)	Yes	Surface	None	Copper	OH/UG	UL/MEG
200	4	2	8	3	TSMR420CSFLFMG									
150	8	4	16	6	TSMR815CSFLFMG									
200	8	4	16	6	TSMR820CSFLFMG									
	20	4	40	18	40	TSMR2020CSCUFMG			No					

Class 320 / Ringless / Single-Phase, 3 Wire, 120/240 Vac with Bonded Neutrals

300	8	4	16	6	16	TSDR830USCU	Ringless	Outdoor (NEMA 3R)	Yes	Surface	Lever Bypass	Copper	UG	UL/MEG
400	8	4	16	6	16	TSDR840UFCU								

Meter Main Factory Installed / Ringless / Single-Phase, 3 Wire, 120/240 Vac with Bonded Neutrals

100	0	0	0	0	0	TM10RMCFMG ¹	Ringless	Outdoor (NEMA 3R)	Yes	Surface	None	Copper	OH/UG	UL/MEG
125	0	0	0	0	0	TM12RMCFMG ¹								
150	0	0	0	0	0	TM15RMCFMG ¹								
200	0	0	0	0	0	TM20RMCFMG ¹								

Meter Socket Load Center / Ringless / Single-Phase, 3 Wire, 120/240 Vac

This is a Service Entrance MLO rated load center. No more than 6 circuits may be added in total in accordance with NEC code concerning service entrance load centers.

200	6	6	0	0	0	TSLR1220FSAL	Ring Type	Outdoor (NEMA 3R)	Yes	Flush	None	Aluminum	OH/UG	UL/MEG
-----	---	---	---	---	---	--------------	-----------	-------------------	-----	-------	------	----------	-------	--------

¹Devices include removable closing cap. Order hub separately.



TSDR840UFCU

