


MULTIPLES OF AMPERE SETTING (CONTINUOUS)



GE Consumer & Industrial -
Electrical Distribution

Sensor Rating (Amperes)

200, 400, 600, 800, 1000, 1200 amperes
2000A Frame — 1600 amperes

Voltage Rating

600 Vac

Frequency Rating

50/60 Hertz

**Insulated Case Circuit Breaker
POWER BREAK® with VersaTrip®**

Types TPSS, THSS
Long-time, Short-time and
Instantaneous Time-current Curves


Curves apply at 50/60 Hertz and
from -20°C to +55°C breaker ambient.

GES-6163A

Adjustments

Long-time Delay Unit: Continuous current settings are 60, 70, 80, 90 and 100% of sensor rating. Time-delay bands are maximum, intermediate and minimum.
Short-time Delay Unit: Pick-up current settings are 3x, 4x, 5x, 6x, 7x and 8x multiples of long-time unit setting. Time-delay bands are maximum, intermediate and minimum.
Instantaneous Unit: Pick-up current settings are 3x, 4x, 5x, 6x, 8x and 10x multiples of long-time unit setting.
Instantaneous Over-ride: Set at 15x sensor ampere rating when the adjustable instantaneous unit is omitted.

MULTIPLES OF AMPERE SETTING (CONTINUOUS)



MULTIPLES OF AMPERE SETTING (CONTINUOUS)

Multiples of Sensor Ampere Rating

GENERAL ELECTRIC

Sensor Rating (Amperes)
 200, 400, 600, 800,
 1000, 1200, amperes
 2000A Frame - 1600 amperes

Voltage Rating
 600 volts ac

Frequency Rating
 50/60 Hertz

INSULATED CASE CIRCUIT BREAKER
POWER-BREAK®
 With **VersaTrip®**
 Types TPSS, THSS Long-time, Short-time
 and Instantaneous Time-current Curves

(Curves apply at 50/60 Hertz and from -20C to +55C breaker ambient)

GES-6163A
 Adjustments

Long-time Delay Unit: Continuous current settings are 60, 70, 80, 90 and 100% of sensor rating. Time-delay bands are maximum, intermediate and minimum.

Short-time Delay Unit: Pick-up current settings are 3x, 4x, 5x, 6x, 7x and 8x multiples of long-time unit setting. Time-delay bands are maximum, intermediate and minimum.

Instantaneous Unit: Pick-up current settings are 3x, 4x, 5x, 6x, 8x and 10x multiples of long-time unit setting.

Instantaneous Over-ride: Set of 15x sensor ampere rating when the adjustable instantaneous unit is omitted.