

Durable Outdoor Power Outlets

Midwest Electric delivers durable, dependable outdoor power where you need it. From building sites to barns, sheds and back yards, we help you power the great outdoors!

- G90 galvanized steel construction for superior corrosion protection
- Durable polyester powder coat finish resists chipping and fading
- Units available in attractive dark green paint
- Weather resistant and tamper resistant GFCI receptacles
- NEMA 3R weatherproof enclosure
- Compact design saves space
- Pre-assembled enclosure reduces installation time
- Padlock provision helps prevent unauthorized access
- Cover design allows cords to exit while maintaining NEMA 3R integrity
- Rolled edge door provides extra cord protection



U010010GRP



U012010GRP



U025S



U010S010GRP



Durable Outdoor Power Outlets

Specifications


Model Number	Receptacles	No. of GFIs	Amps	Volts	Cabinet Size (in.)	Enclosure Color	Weight (lbs.)	Std. Pkg.	cUL ^{us}
U010010GRP	5-20R2GFI	1	20	120	5 x 7	Green	4.5	1	Yes
U010S010GRP	5-20R2GFI & Switch	1	20	120			4.5	1	
U012010GRP	5-20R2GFI	2	20	120			4.5	1	
U025S	L6-20R Twist Lock & Switch	0	20	120		Gray	4	4	
U013	R32U	0	30	120			4.5	4	
U054	14-50R	0	50	120/240			5	4	

Wire Ranges


Connector	U025S & U010S010GRP				U010010GRP*		U012010GRP				U013*		U054*	
	Copper		Aluminum		Copper		Copper		Aluminum		Copper		Copper	
	Solid	Stranded	Solid	Stranded	Solid	Stranded	Solid	Stranded	Solid	Stranded	Solid	Stranded	Solid	Stranded
Line	14-10	14-10	-	-	14-10	14-10	14-10	14-10	-	-	14-10	14-10	12-8	12-4
Load	14-10	14-10	-	-	14-10	14-10	14-10	14-10	-	-	-	-	-	-
Neutral	14-10	14-10	-	-	14-10	14-10	14-10	14-10	-	-	14-10	14-10	12-8	12-4
Equipment Ground	12-8	12-2	12-8	12-2	12-8	12-2	12-8	12-2	12-8	12-2	12-8	12-2	12-8	12-2

*Aluminum wire not applicable.


Layouts



Dimensions



Knockout



Knockout Key

A = 1/2", 3/4"
 B = 1/2", 3/4", 1"
 C = 1/24", 3/4", 1", 1-1/4"

Information provided is subject to change without notice. Please verify all details with Midwest Electric Products. All values are design or typical values when measured under laboratory conditions, and Midwest makes no warranty or guarantee, express or implied, that such performance will be obtained under end-use conditions.

Midwest Electric Products
 305 Gregson Drive
 Cary, NC 27511
 Customer Service: 866-685-0577 • Fax: 804-965-1041
www.midwestelectric.com

© 2019 Midwest Electric Products

MET-007B (12/19)

