

# MAIN SWITCH MODULE

**CATALOG NO. TMPFT4R  
TYPE 3R ENCLOSURE - RAINPROOF - 400AMP.  
120/240V AC 1 PHASE-3 WIRE**

For use with TMP or TMPR meter modules and TMP main lug modules. Continuous load current not to exceed 80% of the rating of fuses employed in other than motor circuits.

REPLACEMENT PARTS	TORQUE MAIN BUS JOINT BOLTS 300 LB-INS																	
<table style="width: 100%; border-collapse: collapse;"> <tr><td style="width: 50%;">End Cap - Right (Deep)</td><td style="width: 50%;">TMECR</td></tr> <tr><td>End Cap - Left (Flat)</td><td>TMECL</td></tr> <tr><td>Switch Assembly (Complete)</td><td>TMPFTS4</td></tr> <tr><td>Front Cover</td><td>TMFC2</td></tr> <tr><td>Drip Hood</td><td>TMDH9</td></tr> <tr><td>Handle</td><td>TMPFH1</td></tr> <tr><td>Hardware Kit</td><td>TMPMSK1</td></tr> <tr><td>Shroud</td><td>TMPSH1</td></tr> </table>	End Cap - Right (Deep)	TMECR	End Cap - Left (Flat)	TMECL	Switch Assembly (Complete)	TMPFTS4	Front Cover	TMFC2	Drip Hood	TMDH9	Handle	TMPFH1	Hardware Kit	TMPMSK1	Shroud	TMPSH1	Suitable only for top feed. Order rainproof hubs from table below.	
End Cap - Right (Deep)	TMECR																	
End Cap - Left (Flat)	TMECL																	
Switch Assembly (Complete)	TMPFTS4																	
Front Cover	TMFC2																	
Drip Hood	TMDH9																	
Handle	TMPFH1																	
Hardware Kit	TMPMSK1																	
Shroud	TMPSH1																	
	Conduit Size	Cat.No.																
	1/2	343L647G3																
	3/4	343L647G4																
	1	343L647G5																
	1-1/4	343L647G6																
	1-1/2	343L647G7																
	2	343L647G8																
	2-1/2	343L647G9																
	3	343L647G10																
	3-1/2	343L647G11																
	4	343L647G12																
<b>SUITABLE FOR USE AS SERVICE EQUIPMENT</b>																		
<b>USE COPPER OR ALUMINUM WIRE USE 75°C WIRE</b>																		

## LUG SPECIFICATIONS

Function	Wire Size CU-AL AWG/MCM	Torque, Lb.-Ins.
Line Terminals	(1) 1/0-750 or (2) 1/0-300	550
Neutral Terminal	(1) 1/0-750 or (2) 1/0-300	550
Grounding Terminal	4-300	250

## SHORT CIRCUIT CURRENT RATING

This module is U.L. listed for use on circuits delivering not more than 100,000 RMS symmetrical amperes at 240 volts maximum when Class T fuses are installed. The short circuit rating is limited to the lowest marked short circuit rating of the TMP or TMPR meter module or TMP main lug module.

