



The AC values below are current ratings per phase.
 these maximum and nominal ratings should be considered when choosing the appropriate AC over current protection device.
 NEC (National Electric Code) Section 210-20a rules must be applied.
 DC current rating is the maximum battery discharge current which the UPS allows.

USP rating	Rectifier AC Input		Bypass AC Input		Common AC Input		DC Input (See Note 4)
	Power Block QTY	Nom.	Max.	Nom.	Max.	Nom.	
160 kW / 160kVA	1	202 A	230 A	193 A	202 A	230 A	392 A

Size of Branch circuit over current protection - All Models: -
"CAUTION - To Reduce the risk of fire, only connect UPS to the circuit provided with (see below) Maximum amperes branch circuit over current protection in according with the NEC, NSI / NFPA 70"

USP rating	Rectifier AC Input		Bypass AC Input		Rectifier AC Input		DC Input (See Note 4) 80% / 100%
	80% Rated Bkr	100% Rated Bkr	80% Rated Bkr	100% Rated Bkr	80% Rated Bkr	100% Rated Bkr	
160 kW / 160kVA	300 A / 250 A	300 A / 250 A	250 A / 200 A	250 A / 200 A	300 A / 250 A	300 A / 250 A	400 A / 400 A

- NOTE:
- 1) Bypass and Rectifier input must be connected with clockwise phase rotation.
 - 2) For eBoost operating mode, the Bypass input must be fed from a grounded-WYE electrical system (4 Wire+Ground). Consult factory for 3-wire Input system.
 - 3) UPS is configured for single input as standard. UPS may be configured for dual input by removing the jumpers between Rectifier and Bypass inputs.
 - 4) An external battery breaker must be provided that includes a 24VDC undervoltage release and Aux contacts.
 - 5) UPS designed for installation in an electrical system with 65kA contact.
 - 6) Contact General Electric for details concerning operational with 3-wire input.

Date		27.11.2018		UPS schematic diagram		REPLACE		REVISION		1	
Des.		Barbarani R.		GE Proprietary and Confidential		SERIES		REFERENCE NUMBER		0001048305	
Check		Condolfi S.		All rights for transmission, duplicating or reprinting reserved		2		7		Pag. 1	
Revision		1		Name		Bobliano C.		8		Pag. 1	



TLE Series
 160kVA 3ph UL