



The AC values below are current ratings per phase.
 these maximum and nominal ratings should be considered when choosing the appropriate AC over current protection device.
 NEC (National Electric Code) Section 210-20a rules must be applied.
 DC current rating is the maximum battery discharge current which the UPS allows.

USP rating	Rectifier AC Input		Bypass AC Input		Common AC Input		DC Input (See Note 4)
	Power Block QTY	Nom.	Max.	Nom.	Max.	Nom.	
300 kW / 300kVA	2	378 A	430 A	361 A	378 A	430 A	727 A

"CAUTION - To Reduce the risk of fire, only connect UPS to the circuit provided with the NEC, NSI / NFPA 70" ampere branch circuit over current protection in accordance with the NEC, NSI / NFPA 70"

Size of Branch circuit over current protection - All Models:-

USP rating	Rectifier AC Input		Bypass AC Input		Rectifier AC Input		DC Input (See Note 4) 80% / 100%
	80% Rated Bkr	100% Rated Bkr	80% Rated Bkr	100% Rated Bkr	80% Rated Bkr	100% Rated Bkr	
300 kW / 300kVA	600 A / 450 A		500 A / 400 A		600 A / 450 A		800 A / 800 A

NOTE:

- 1) Bypass and Rectifier input must be connected with clockwise phase rotation.
- 2) For eBoost operating mode, the Bypass input must be fed from a grounded-WYE electrical system (4 Wire+Ground). Consult factory for 3-wire Input system.
- 3) UPS is configured for single input as standard. UPS may be configured for dual input by removing the jumpers between Rectifier and Bypass inputs.
- 4) An external battery breaker must be provided that includes a 24VDC undervoltage release and Aux contacts.
- 5) UPS designed for installation in an electrical system with 65kA contact.
- 6) Contact General Electric for details concerning operational with 3-wire input.

Date		27.11.2018		Date		27.11.2018	
Des.		Borbonni R.		Des.		Borbonni R.	
Check		Condoffi S.		Check		Condoffi S.	
Name		Bobliano C.		Name		Bobliano C.	
Revision		1		Revision		2	
Date				Date			
Condit.				Condit.			

UPS schematic diagram

GE Proprietary and Confidential

GE C & I SA

CH-6595 Riazziolo Locarno

TLE Series

300kVA 3ph UL

REPLACE SERIES 2

REVISION REFERENCE NUMBER 0001048309

1

Pag. 1