



TYPICAL SCHEMATIC FOR:
BLW-220
BLW-230

- NOTES:**
1. POWER WIRING TO BE SIZED FOR LOAD.
 2. WIRE SHALL BE COLOR CODED AS FOLLOWS:
 - BLACK - LOAD AND CONTROL AT LINE VOLTAGE
 - RED - AC CONTROL CIRCUITS
 - BLUE - DC CONTROL CIRCUITS
 - YELLOW - CONTROL CIRCUITS WIRED FROM AN EXTERNAL POWER SOURCE
 - GREEN - GROUNDING CONDUCTORS
 - WHITE - NEUTRAL
 3. USE #14 GAUGE MINIMUM STRANDED MACHINE TOOL WIRE FOR CONTROL WIRING.
 4. WIRING SHOWN BROKEN IS EXTERNAL TO PANEL.
 5. ALL WIRES MUST BE TAGGED AT BOTH ENDS, TERMINAL AND WIRE NUMBER TO BE THE SAME.
 6. CONTROL VOLTAGE IS 120 VAC.

GE Energy

MULTIPULSE DRIVE PANEL
100 HP 480VAC
18 PULSE, NON-BYPASS

REV.	DATE	REVISION DESCRIPTION	DWG NO.	DATE	REV
A	06/27/2012	PRIMARY SUBMITTAL	1217412	08/27/2012	C
B	02/26/2013	REVISED			
C	03/05/2013	REVISED			

REV.	DATE	REVISION DESCRIPTION
A	06/27/2012	PRIMARY SUBMITTAL
B	02/26/2013	REVISED
C	03/05/2013	REVISED