



| CUSTOMER TERMINATION | | | |
|----------------------|--------------------------------------|----------------|---------------|
| LOCATION | CONNECTION TYPE | HOLE SIZE | HOLE QTY |
| PRIMARY BUS BARS | STANDARD BUS BAR (LUGS ARE OPTIONAL) | .41 [10.3] DIA | 1 PER BUS BAR |
| SECONDARY BUS BARS | | | |

APPROX TOTAL WEIGHT LBS [KG]
AL WINDINGS: 471 [214]
CU WINDINGS: 494 [224]

kVA RATING:
K-FACTOR:
PRI VOLTAGE:
SEC VOLTAGE:
FREQ (Hz):
TEMP RISE:
WINDING MATL:
ES SHIELD:
SOUND LVL (dB):

- NOTES:**
- 1) ALL UNITS ARE UL LISTED AND ARE DESIGNED PER NEMA ST-20 STANDARDS.
 - 2) TRANSFORMER IS DESIGNED FOR FLOOR MOUNTING. OPTIONAL WALL MOUNTING BRACKETS ARE NOT AVAILABLE FOR THIS DESIGN/STYLE.
 - 3) TRANSFORMER IS DRY TYPE, CLASS AA, WITH VENTILATED ENCLOSURE FOR INDOOR USE. OPTIONAL RAINSHIELD KITS ARE INCLUDED TO CONVERT UNIT TO TYPE 3R OUTDOOR USE WITHOUT VOIDING THE WARRANTY.
 - 4) APPLICABLE WHEN OPTIONAL RAINSHIELDS ARE INSTALLED. RAINSHIELDS ARE SHIPPED IN KITS FOR FIELD INSTALLATION.
 - 5) CABLE ENTRANCE IS PERMITTED THROUGH THE TOP OR BOTTOM OF THE BREAKER BOX OR UP TO 4" [102 MM] FROM THE BOTTOM OF EITHER SIDE OF THE BOX ONLY. CABLE ENTRANCE IS NOT PERMITTED THROUGH THE FRONT OR REAR OF BREAKER BOX.
 - 6) FOR LIFTING OTHER THAN WITH A FORK TRUCK, REMOVE TOP COVER AND USE 1" [25 MM] DIAMETER HOLES IN THE TOP CORE CLAMPS.
 - 7) ENCLOSURE PAINT COLOR IS ANSI #61 GRAY.
 - 8) 6" [152 MM] MINIMUM CLEARANCE IS REQUIRED FROM ALL WALLS.
 - 9) CUSTOMER CABLE MUST BE RATED 75° C OR HIGHER AND MAY BE EITHER COPPER OR ALUMINUM.

| | | |
|--|--|---|
| JOB NAME: SPEEDI PROP: | UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCH [MM] |  Transformers |
| | THIRD ANGLE PROJECTION  | |
| www.geindustrial.com/transformers | | CATALOG # |
| CAD DRAWING: 303B424AAP030 | SHEET 1 OF 1 | REV 0 |