

-NOMENCLATURE-
M-LINE CONTACTOR
I-INDICATING LIGHT
FU-FUSE
OL- THERMAL OVERLOAD RELAY
X-INDICATES CONTACT CLOSED

FOR STARTER WITHOUT DISCONNECT MEANS - WIRE LINE DIRECT TO L1,L2 & L3 ON STARTER.


NOTE: REFER TO THE NATIONAL ELECTRICAL CODE. ADDITIONAL CONTROL CIRCUIT OVER-CURRENT PROTECTION MAY BE REQUIRED.

FOR EXTRA AUXILIARY CONTACTS - A MAXIMUM OF 3 CONTACTS MAY BE ADDED AT POSITIONS W,X,Y & Z.


FOR CSA - GND KIT
1/2 IN. CONDUIT 55-213403G001
3/4 IN. CONDUIT 55-213403G002
1 IN. CONDUIT 55-213403G003
1-1/4 IN. CONDUIT 55-213403G004

	CR305	CR307	CR308	CR387
USE 75°C COPPER CONDUCTORS ONLY, FOR FIELD WIRING. TORQUE	50 LB-IN	50 LB-IN	50 LB-IN	50 LB-IN
LINE AND LOAD TERMINALS AS SHOWN AT RIGHT:	AS MARKED	50 LB-IN	50 LB-IN	50 LB-IN


START-STOP PUSHBUTTON ELEMENTARY




3 POSITION SELECTOR SWITCH ELEMENTARY



2 POSITION SELECTOR SWITCH ELEMENTARY



WIRING DIAGRAM
FVNR SIZE 2

AN #	THIRD ANGLE PROJECTION	SHEET #
09-9112		1 OF 1

DWG NO.	DATE	REV
55-192550	08/17/2009	5