




GE reserves all rights in this document and in the information contained therein. Reproduction, use or disclosure to third parties without express authority is strictly forbidden.

REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED

	Weight kg(lb)		
FRAME	40-80A	125A	250A
2P	7.6(16.8)	9.8(21.6)	10.5(23.2)
3P	8.2(18.1)	10.8(23.8)	11.9(26.3)
4P	8.8(19.4)	11.8(26)	13.3(29.3)



FRONT COVER DETAIL
(OUTSIDE VIEW)

1. 4-POLE SWITCH SHOWN. FOR 2 OR 3 POLE OMIT RIGHT HAND POLES AS SHOWN, SEE TABLE BELOW.

	T1	T2	T3	TN
4 POLE	Y	Y	Y	Y
3 POLE	Y	Y	Y	-
2 POLE	Y	Y	-	-

- DO NOT RUN CABLES IN FRONT OF SWITCH. KEEP FRONT OF CONTROLLER FREE FROM RUNNING CABLES
- MAINTAIN ELECTRICAL CLERANCE OF 1"(25MM)MIN. BETWEEN LIVE METAL PARTS AND GROUNDED METAL.
- ALL DIMENSIONS ARE FRE REFERENCE ONLY.
- ALL DIMENSION SHOWN IN MILLIMETERS (INCHS)

FRAME	a	b	c	d	e
40-80A	108.4 (4.26)	21.6 (0.85)	125.5 (4.94)	28 (1.1)	197 (7.76)
125A	145 (5.7)	30 (1.18)	125.5 (4.94)	18 (0.71)	215.5 (8.484)
250A	148.3 (5.838)	40 (1.575)	125.5 (4.94)	18 (0.71)	215.5 (8.484)

FIRST ANGLE PROJECTION 	SIGNATURES		DATE	GE Energy Digital Energy GENERAL ELECTRIC COMPANY
	DRAWN BY	CHECKED BY		
DIMENSIONS ARE IN MILLIMETERS	APPROVED BY			TITLE GTX 40-250A OPEN STYLE
				Material
Part must conform to SI 900000 Sect. 4, Toxicity Procedure	SIMILAR TO:			SIZE A3
	SOLID MODEL:			DRAWING 57C-1051_1
CRITICAL TO QUALITY CHARACTERISTIC				Weight
				REV
				SCALE:
				REF. No:
				SHEET 1 OF 2
				METRIC