




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
E	S-8333	04/12/06	NB MAS


CABINET	NO. POLES	WIRE BENDING SPACE		WIRE GUTTERS	
		P(TOP)	R(BOTTOM)	S(LEFT)	T(RIGHT)
F-1827MP	2,3,4	16 3/8 (416)	17 13/16 (452)	3 3/4 (95)	5 (127)



- NOTES:**
1. MATERIAL: 14 GA. 1018 HRS .074(2) REF. (F-1827MP)
 2. FINISH: ANSI 61 GREY
 3. ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SHOWN IN INCHES(MILLIMETERS).
 4. CONSTRUCTION PER UL 1008

FOR ADDITIONAL INFO REFER TO APPLIED PRACTICES UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	SIGNATURES	DATE	GE Zenith Controls TITLE NEMA 3R ENCLOSURE ZTX
TOLERANCES ON: 2 PL. DECIMALS ± .020 3 PL. DECIMALS ± .005 ANGLES ± 1° FRACTIONS ± 1/64 FINISH ✓	MODEL MAS	1/26/05	
AutoCad Generated	ENGRG MAS	1/26/05	FIRST MADE FOR: ZTX MX60 SIZE D CAGE CODE DWG NO 58C-1009 SCALE: NA SHEET 2 OF 2

GE PROPRIETARY AND CONFIDENTIAL INFORMATION
 This document is the property of General Electric Company ("GE") and contains proprietary information of GE. This document is loaned on the express condition that neither it nor the information contained therein shall be disclosed to others without the express written consent of GE Industrial Systems, and that the information shall be used by the recipient only as approved expressly by GE Industrial Systems. This document shall be returned to GE upon its request. This document may be subject to certain restrictions under U.S. export control laws and regulations.



D
C
B
A

D
C
B
A