



# Transformer

by ABB




\*1M000000\*

**Catalog Number**      **Type QL**  
**9T10A1063G31**


45.0 KVA    60 HZ    3 PH    3.4 % IMP  
40 C AMB.    115 C RISE    220 C SYSTEM    IS-19C

PRIMARY (H)    480 VOLTS (LINE-LINE)  
SECONDARY (X)    380 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1	503
2	493
3	480
4	467
5	457
6	443
7	433



### COIL TAP ARRANGEMENT



<b>NET WGT</b>	<b>INSPECTION &amp; FINAL TEST</b>
444 LB	
201.4 Kg	<b>NOG</b>
88735	N137!
UX73A	091021



LISTED 769G

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1072G06

**BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001**  
 ALUMINUM CONDUCTOR    PRIMARY: 10 KV BIL    SECONDARY: 10 KV BIL  
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.  
 CHECK ADDITIONAL NEC AND LOCAL CODE

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency


ASSEMBLED IN MEXICO

X3 H3 X2 H2 X1 H1 -

Note: standard

Outline: 303B111GEUXP73A

X3 H3 X2 H2 X1 H1



\*2M000000\*

X3 H3 X2 H2 X1 H1



\*3M000000\*