



Transformer

—
by ABB




1M000000

Catalog Number **Type QL**
9T10A1067


225.0 KVA 60 HZ 3 PH 5.9 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (H) 480 VOLTS (LINE-LINE)
SECONDARY (X) 380 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	505
2-3	493
3-4	480
4-5	469
5-6	457
6-7	445
7-8	433



COIL TAP ARRANGMENT



NET WGT	INSPECTION & FINAL TEST
1450 LB	NOG
657.7 Kg	N139!
89124	092021
DY77A	



ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1077G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP009
 ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
 IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
 CHECK ADDITIONAL NEC AND LOCAL CODE

Note:

Outline: 303B112GEDYP77A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency



2M000000



3M000000