

TYPICAL TEST DATA

LV Dry Type Transformer



MODEL #: **9T10A1006G04**

Underwriters' Laboratories Inc. Listed

RATINGS

KVA	150	Conductor	AL
Frequency (Hz)	60	Phase	3
Primary Voltage	480D+2,-4(2.5%taps)	Secondary Voltage	208Y/120
Current Line Primary (A)	180.42	Current Line Secondary (A)	416.36
Frame	DY76A	Insulation System (°C)	220C
K Factor	1	Efficiency level	DoE 2016 (10CFR 431)
Temp. Rise (°C)	150	Average Sound Level (dB)	47

LOSS DATA @ 100% LOAD

Core Loss or No Load Loss @ 100% voltage (Watts)	322.0
Impedance Loss or Coil Loss @ Rise + 20 °C reference (Watts)	<u>2,955.4</u>
Total Loss @ Rise + 20 °C reference (Watts)	3,277.4

DIELECTRIC AND PRODUCTION TESTING

Induce Test @ Twice rated voltage 400 Hz per UL1561 and NEMA ST-20
 Hipot Test for High Voltage winding to Low Voltage and Ground @ 4000 volts 60 Hz, 60 Sec
 Hipot Test for Low Voltage winding to High Voltage and Ground @ 2500 volts 60 Hz, 60 Sec
 Polarity additive in accordance with UL1561 and NEMA ST-20

EFFICIENCY:

DoE 2016 (10CFR 431) Efficiency Level

<u>Load (%)</u>	<u>Efficiency (%)</u>
16	98.45
25	98.79
35	98.83
50	98.84
75	98.62
100	98.33

IMPEDANCE:

Impedance at reference temperature of Rise + 20 °C (Calculated)

%R	2.0
%X	4.1
%Z	4.5
X/R Ratio	2.1

REGULATION:

Regulation at reference temperature of Rise + 20 °C (Calculated)

<u>Power Factor</u>	<u>Regulation (%)</u>
1	2.1
0.9	3.6
0.8	4.1

REFERENCE VALUES:

Inrush Current t= 8.33ms
 (Calculated)
 I_{max}(RMS) ≈ 2715.9 A