



Transformer

by ABB






1M000000

Catalog Number **Type QL**
9T10A1116


150.0 KVA 60 HZ 3 PH 3.1 % IMP
40 C AMB. 150 C RISE 220 C SYSTEM IS-19C

PRIMARY (X) 480 VOLTS (LINE-LINE)
SECONDARY (H) 575 VOLTS (LINE-LINE)

JUMPER CONNECTION	
TAP	VOLTS
1-2	506
2-3	495
3-4	480
4-5	466
5-6	454
6-7	443
7-8	431



COIL TAP ARRANGEMENT



NET WGT
1030 LB
467.2 Kg
89160
DY76A

INSPECTION & FINAL TEST
NOG
N137!
091021



LISTED 769G

H3 - H2 - H1 - -
- X3 - X2 - X1 - -
H3 - H2 - H1 - -
- X3 - X2 - X1 - -

2M000000

3M000000

ENCLOSURE TYPE 2 (IP20). OR RAINPROOF TYPE 3R (IP22) WHEN PROVIDED SHIELD 9T18Y1076G06

ASSEMBLED IN MEXICO

BEFORE HANDLING, INSTALLING AND OPERATING, SEE INSTRUCTION 475A667AAP001
ALUMINUM CONDUCTOR PRIMARY: 10 KV BIL SECONDARY: 10 KV BIL
IN ACCORDANCE WITH NEC SECTION 450-9, ALLOW AT LEAST SIX INCHES CLEARANCE FOR VENTILATION.
CHECK ADDITIONAL NEC AND LOCAL CODE

H3 - H2 - H1 - -
- X3 - X2 - X1 - -
Note: standard

Outline: 303B111GEDYP76A

NEMA CLASS AA DRY TYPE TRANSFORMER

Meets DOE 2016 efficiency